

KFMC 3844 L

MasterCool fridge-freezer

MasterFresh Pro | FoodView | AirClean System | IceMaker | BrilliantLight Pro



- Food stays fresh for up to 5 times longer – MasterFresh Pro
- Everything in full view at all times – FoodView
- Fresh supplies without unpleasant odours – #Longlife AirClean system
- Ice cubes for cold drinks – IceMaker
- Practical illumination with elegant LEDs – #BrilliantLight Pro



EAN: 4002516914587 / Material number: 12866720 /

Old Material Number: 38384410GB

Appliance category	
MasterCool (refrigeration unit XXL)	•
Construction type	
Built-in appliance	•
Integrated appliance	•
Door hinge	Left
Convertible door hinging	•
Side-by-side enabled	•
Design	
Lighting	BrilliantLight Pro
SmartLight	•
User convenience	
Networking with Miele@home	•
FoodView (cameras)	3
Freshness system	MasterFresh Pro + DailyFresh ExtraCool
Longlife AirClean system	•
DynaCool	•
NoFrost	•
DuplexCool Pro	•
SoftClose	•
SelfClose	•
Number of IceMakers with mains water connection	1
IceMaker with mains water connection	•
Push2open	•
FullAccess	•
EasyClean	•
MaxLoad hinge	•
Control system	
Operating concept	M Touch Pro
Precise adjustment	Fridge and freezer temperature
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	Yes
SuperCool&AirClean	•
SuperFreeze	•
No. of temperature zones	3
Sabbath mode	•
Holiday mode	•
Eco mode	•
QuickIce	•
Fridge/Fridge section	
Height-adjustable, full-width tempered glass shelves	1
Height-adjustable, half-width tempered glass shelves	2
Number of VeggieBoxes	1
No. of crisper drawers	2
Door shelves for jars	2

KFMC 3844 L

MasterCool fridge-freezer

MasterFresh Pro | FoodView | AirClean System | IceMaker | BrilliantLight Pro



EAN: 4002516914587 / Material number: 12866720 /


Old Material Number: 38384410GB

Door rack for bottles	1
Freezer/Freezer section	
Number of freezer baskets	3
of which on telescopic runners	2
Efficiency and sustainability	
Energy efficiency class (A–G)	D
Annual energy consumption in kWh	280.00
Energy consumption in 24 h in kWh	0.76
Safety	
Spill-proof glass shelves	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Technical data	
Niche width in mm min.	902
Niche width in mm max.	902
Niche height in mm min.	2134
Niche height in mm max.	2134
Niche depth in mm	610
Appliance width in mm	895
Appliance height in mm	2123
Appliance depth in mm	608
Weight in kg	234.2
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	47
Max. door front weight – freezer, in kg	14
Climate class	SN-T
Refrigerator compartment in l	382
including PerfectFresh zone in l	60
4* freezer compartment in l	197
Total usable capacity in l	579
Storage time in case of fault in h	19
Freezer capacity in kg/24 h	14.00
Acoustic airborne noise emission class (A–D)	C
Sound emissions in dB(A) re 1 pW	39
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	3.0
Replacing lamps	Service
Accessories included	
Ice scoop	•

KFMC 3844 L


MasterCool fridge-freezer

MasterFresh Pro | FoodView | AirClean System | IceMaker | BrilliantLight Pro




KFMC3642R + L, KFMC3844R + L, MasterCool III, PACS, with stainless steel front, installation (*Footnote) (drawing)

Information for KFMC 3642 L + R (US/CD) only, *View from the front, 1. Mains connection cable, L = 3000 mm (118 inch), 2. Water connection L = 1800 mm (70 inch), Information for KFMC 3844 L + R (EU) , 1. Mains connection cable, L = 3000 mm, 2. Water connection L = 1800 mm




KFMC3642R, KFMC3842L, KFMC3844R, KFMC3844L, MasterCool III, installation, panel ready (installation drawing) (US)


Information for KFMC 3642 L + R (US/CD) only, *View from the front, 1. Mains connection cable, L = 3000 mm (118 inch), 2. Water connection L = 1800 mm (70 inch), Information for KFMC 3844 L + R (EU) , 1. Mains connection cable, L = 3000 mm, 2. Water connection L = 1800 mm



KFMC3642R, KFMC3642L, KFMC3844R, KFMC3844L, MasterCool III, PACS, with stainless steel front, integration (drawing)




KFMC3642R, KFMC3842L, KFMC3844R, KFMC3844L, MasterCool III, integration, panel ready (installation drawing) (US)



KFMC3642R, KFMC3842L, KFMC3844R, KFMC3844L, MasterCool III, front view (*Footnote) (installation drawing) (US)

*1. 47 kg, 2. 14 kg




KFMC3632R+L, KFMC3642R+L, KFMC3836R+L, KFMC3834R+L, KFMC3858FD, MasterCool III, frame neutral, installation (drawing)


KFMC 3844 L

MasterCool fridge-freezer


MasterFresh Pro | FoodView | AirClean System | IceMaker | BrilliantLight Pro




KFMC3632R+L, KFMC3642R+L, KFMC3836R+L, KFMC3834R+L, KFMC3858FD, MasterCool III, hinge clearance, installation (drawing)



KFMC3632R+L, KFMC3642R+L, KFMC3836R+L, KFMC3834R+L, KFMC3858FD, MasterCool III, Side-view bottom, installation (drawing)



KFMC3642R, KFMC3642L, KFMC3844R, KFMC3844L, MasterCool III, PACS, with stainless steel front, top view (drawing) (US)



KFMC3642R, KFMC3642L, KFMC3844R, KFMC3844L, MasterCool III, panel ready, top view (installation drawing) (US)