

## DGC 7460 HC Pro

for steam cooking, baking, roasting with networking + HydroClean.



- Large clear text display with sensor controls – DirectSensor
- Perfect results – DualSteam technology
- Crispy outside, succulent inside – combination cooking
- Convenient operation – water container behind automatic panel
- Easy cleaning – HydroClean and stainless steel oven compartment



EAN: 4002516923855 / Material number: 12874480 /  
Old Material Number: 23746003GB

### Construction type and design

Appliance colour Pearl beige

### Construction type and design

Steam combination oven

### Available display languages

Available display languages via MultiLingua

bahasa malaysia, dansk,  
deutsch, english, español,  
français, hrvatski, italiano,  
magyar, nederlands, norsk,  
polski, português, русский,  
română, slovenčina,  
slovenščina, srpski, suomi,  
svenska, türkçe, українська,  
čeština, ελληνικά,  
[?][?][?][?][?][?], [?][?], [?]  
[?][?], [?][?][?][?], [?][?][?]

### Construction type and design

VitroLine

### Convenience features

Rapid heat-up

Pre-heating

External steam generation

Oxygen sensor

Individual humidity settings in combination cooking

Menu cooking without transfer of taste

Prepare plated meals with "Mix & Match"

Automatic programmes with ability to make individual adjustments

Keeping warm

Crisp function

### Operating modes

Fan plus

Conventional heat

Steam cooking

Combination cooking

Combination cooking with Fan plus

Combination cooking with Conventional heat

Combination cooking with grill

Sous-vide

Intensive bake

Fan grill

Grill

Economy grill

Top heat

Bottom heat

Cake plus

Eco fan heat

Eco steam cooking

Defrost

Roast with moisture

## DGC 7460 HC Pro

for steam cooking, baking, roasting with networking + HydroClean.



EAN: 4002516923855 / Material number: 12874480 /  
Old Material Number: 23746003GB

Reheat	•
Plate warming	•
Automatic programmes	•
Country-specific automatic programmes	•
Special applications	•
<b>User convenience</b>	
Networking with Miele@home	•
Display	DirectSensor
SoftOpen	•
SoftClose	•
MultiLingua	•
Motorised lift-up control panel with SoftClose	•
Quantity-independent cooking	•
Steam cooking on up to 4 levels at the same time	•
Automatic menu cooking	•
Steam reduction before end of programme	•
Time of day display	•
Date display	•
Minute minder	•
Programmable start of cooking duration	•
Programmable end of cooking duration	•
Programmable cooking duration	•
Actual temperature display	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Recommended temperature	•
User programmes	•
Sabbath programme	•
Individual settings	•
<b>Efficiency and sustainability</b>	
Energy efficiency class (A+++ – D)	A+
Power rating in off mode in W	0.3
Power rating in standby mode in W	0.8
Power rating in networked standby in W	2.0
Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
<b>Cleaning and care</b>	
Stainless-steel oven compartment with linen structure	•
Hinged grill element	•
External steam generator	•
HydroClean	•
Soak programme	•
Rinse programme	•
Oven compartment drying programme	•
Quick-release side racks	•
Removable stainless-steel side racks	•
Automatic descaling	•

## DGC 7460 HC Pro

for steam cooking, baking, roasting with networking + HydroClean.

EAN: 4002516923855 / Material number: 12874480 /

Old Material Number: 23746003GB

CleanGlass door	•
<b>Steam techn./water supply</b>	
DualSteam	•
Steam generator power in kW	3.30
Fresh water container volume in l	1.4
Fresh water container behind motorised control panel	•
Condensate container behind motorised lift-up control panel with SoftClose	•
Drain filter	•
<b>Safety</b>	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Vapour cooling system	•
Sensor lock	•
<b>Technical data</b>	
Oven compartment volume in l	67
No. of shelf levels	4
Appliance dimensions (W x H x D) in mm	595 x 596 x 567
Numbered shelf levels	•
Door hinge	Bottom
Oven light	BrilliantLight
Oven temperature regulation min. in °C	30
Oven temperature regulation max. in °C	230
Electronic steam oven temperature regulation min. in °C	40
Electronic steam oven temperature regulation max. in °C	100
Niche width min. in mm	560
Niche width max. in mm	568
Niche height min. in mm	590
Niche height max. in mm	595
Niche depth in mm	550
Appliance width in mm	595
Appliance height in mm	596
Appliance depth in mm	567
Weight in kg	46.4
Total rated load in kW	3.45
Voltage in V	230
Frequency in Hz	50
Fuse rating in A	16
Number of phases	1
Mains cable with plug	•
Length of supply lead in m	2
Replacing lamps	Service
<b>Accessories included</b>	
Universal tray with PerfectClean HUBB 71	1
Baking and roasting rack with PerfectClean HBBR 71	1
Removable side runners (pair)	1
Perforated stainless-steel cooking containers	1
Solid stainless steel cooking containers	1

DGC 7460 HC Pro

for steam cooking, baking, roasting with networking + HydroClean.




EAN: 4002516923855 / Material number: 12874480 /  
Old Material Number: 23746003GB

HydroClean cleaning agent	1
Descaling tablets	2


## DGC 7460 HC Pro

for steam cooking, baking, roasting with networking + HydroClean.




H7000 handle, glass, installation drawings


1) 400 mm, 2) 360 mm, 3) 47 mm, 4) 27 mm, 5) 32.5 mm




Installation DGC XXL, ESW7x20 installation drawings




Installation\_DGC\_XXL\_ESW7x10\_EVST010 installation drawings




built-in DGC XXL, installation drawing




built-in DGC XXL build-under, installation drawing  
Worktop overhang ≤ 29 mm



screw joint DGC XXL, installation drawing



DGC7x4x swivel range of the aperture, installation drawings



side view DGC XXL, installation drawings