

## Triflex HX3 Cat & Dog Cordless stick vacuum cleaners

high suction power | up to 70 min running time | flooring detection | HEPA | pet hair attachment



- Dust pickup >99.99%\* for thorough and hygienic deep cleaning
- Boost mode: for faster cleaning of heavily soiled areas
- Running time: up to 70 minutes\*\* with VARTA lithium-ion rechargeable battery.
- Patented\*\*\* 3-in-1 design incl. self-standing feature for parking
- HEPA filter: 99.999%\*\*\*\* exhaust air filtration for the purest ambient air
- FloorDetect: automatic flooring detection and power adjustment
- BrilliantLight: particularly bright LED front light for maximum dust detection
- Display: shows time left and important data for stress-free vacuuming
- Twist2open: for hygienic and easy emptying of the dust container
- Carefully developed and manufactured in Germany by Miele & Cie. KG
- Electro Compact brush for removing pet hair

\* When picking up dust on hard floors with cracks, we achieve > 100% dust pickup in power level HI, measured according to IEC 62885-4:2024

\*\* Valid for power level MIN without connected Multi Floor XXL electrobrush

\*\*\* Patent: DE 10 2016 105 475 B4

\*\*\*\* 99.999% according to IEC 62885-4:2020/HEPA according to EN 1822-1:2019

EAN: 4002516922483 / Material number: 12878410 /  
Old Material Number: 41WDL032GB

General information	
Model identifier	Triflex HX3 Cat & Dog
Manufacturer material number	12878410
EAN number	4002516922483
Construction type	
Cordless stick vacuum cleaners	•
Product brand	Triflex HX3
Motor type	Digital Efficiency Motor
Product type	SWDLO
Appliance type and design	
Appliance colour	Obsidian black
Cleaning	
Vortex Technology	•
MultiFloor XXL SEB 435 electrobrush with BrilliantLight	•
User convenience	
Park system for pauses during vacuuming	•
Exchangeable Li-Ion battery	•
3-in-1 design	•
Filter system	
ComfortClean	•
Exhaust filter	HEPA lifetime filter
Dustbag volume in l	0.5
Technical data	
Battery type	Li-ion
Nominal battery capacity in mAh	2500
Volume in dB	74.0
Width in mm	260
Height in mm	1297
Depth in mm	280
Weight in kg	3.6
Volt	25,2
High level running time PowerUnit solo	70
LOW level running time with electrical accessories	38
High level running time with electrical accessories	15
Cleaning area in m <sup>2</sup>	160
Recharging time in min.	240
Accessories included	
HX-DB dusting brush	•
XL HX-UN upholstery nozzle	•
HX-CN crevice nozzle	•
HX-AH accessories holder	•
MultiFloor XXL electrobrush with BrilliantLight	•
Cleaning tool	No
Wall Mount	•
Power supply unit	•
HX-EC 10 Electro Compact	•