

PWM 935 [SI DV DD SOM]

Professional washing machine, steam heating (indirect)
for marine applications – freely programmable. 35 kg load size.



- Volume of the honeycomb drum 320 l, maximum load size 35.0 kg
- 19 % less water consumption and 40 % less energy consumption*
- Short subsequent drying thanks to BoostSpin
- Ideal operation thanks to colour touch display – M Touch Pro Plus
- Connected for the future using LAN and WiFi

* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

EAN: 4002516928492 / Material number: 12887750 /
Old Material Number: 51935008SOM

Construction type and version

Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Control panel colour	Stainless steel
Maximum load with a load ratio of 1:9 in kg	35.0
Load ratio	1:9
Load in kg	35.0
Drum volume in l	320
Door opening [Ø] in mm	415
Door opening angle in degrees	180
Door hinge	right
Automatic door lock	•
Maintenance-free motor with frequency converter	•
Patented stainless steel honeycomb drum 2.0	•

Application

Suitable for offshore use	•
Suitable for marine use	•

Performance data

Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	6.80
Specific energy consumption for cold water connection in kWh/kg	0.18
Specific water consumption for hot water connection in l/kg	6.50
Specific energy consumption for hot water connection in kWh/kg	0.05
Water consumption with cold water connection in l	238.6
Water consumption for cold water connection in Mops standard 60 °C programme in l	392.5
Energy consumption with cold water connection in kW	6.34
Energy consumption for cold water connection in Mops standard 60 °C programme in kWh	7.20
Programme duration in minutes with cold water connection	51
Water consumption with hot water connection in l	226.5
Water consumption for hot water connection in Mops standard 60 °C programme in l	404.2
Energy consumption with hot water connection in kW	1.75
Energy consumption for hot water connection in Mops standard 60 °C programme in kWh	2.61
Programme duration in minutes with cold water and hot water connection	47
Water consumption in ECO programme with cold water connection in l	224.4
Energy consumption in ECO programme with cold water	4.18
Programme duration in minutes with cold water connection in ECO programme	37

PWM 935 [SI DV DD SOM]

Professional washing machine, steam heating (indirect)
for marine applications – freely programmable. 35 kg load size.



EAN: 4002516928492 / Material number: 12887750 /
Old Material Number: 51935008SOM

Water consumption in ECO programme with hot water connection in l	217.4
Energy consumption in ECO programme with hot water	0.67
Programme duration in minutes with cold water and hot water connection in ECO programme	34
Programme running time in minutes for Mops standard 60 °C programme with cold water connection	52
Programme running time in minutes for Mops standard 60 °C programme with hot water connection	50
Residual moisture with cold rinse in %	50
Residual moisture with hot rinse in %	43
Residual moisture when processing cleaning cloths in %	12
Spin speed in rpm	1060
g factor	502
Tested operating hours	30000
Control system	
Control system	M Touch Pro Plus
Programmability	Freely programmable
Customer-specific pre-configuration possible	•
Max. delay start in h	Freely selectable
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Language can be selected easily at any time	•
Option to enter weight prior to start of programme	•
Standard/target grp programmes	
Basic programmes	•
Programmes for offshore use	•
Programmes for marine use	•
Dispensing	
Detergent drawer	4 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•
Standard electrical connection	
Heating type	Indirect steam
Electrical connection	3 AC 400V 50 HZ
Steam heater rating in kW	50.00
Total connected load in kW	6.10
Fuse rating in A	16
Possible voltage variant 1	
Electrical connection	3 AC 400V 60 HZ
Total connected load in kW	6.10
Fuse rating in A	16
Water connection/drainage	
Hard water (optional) [number]	2 x 1/2" w/ 3/4" union
Dump valve	DN 70
Dimensions and weight	
External dimensions, height in mm	1646

PWM 935 [SI DV DD SOM]

Professional washing machine, steam heating (indirect)
for marine applications – freely programmable. 35 kg load size.

EAN: 4002516928492 / Material number: 12887750 /
Old Material Number: 51935008SOM

External dimensions, width in mm	1090
External dimensions, depth in mm	1275
External dimensions, gross height in mm	1793
External dimensions, gross width in mm	1365
External dimensions, gross depth in mm	1425
Net weight in kg	665.0
Gross weight in kg	722
Maximum floor load in N	9540

Emissions data

Emission sound pressure level in the workplace	71 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	6.10

Features

Patented pre-spin	•
Cloth reprocessing	•
Imbalance monitoring	•
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Efficient scoop-and-ladle ribs	•
EcoSpeed	•
BoostSpin	•
Temperature monitoring	•
Automatic load control+	•
Volumetric flow meter (optional)	•
Weighing plinth (optional)	•
Add laundry	•
Programme selection via colour frame	•
Efficient fast spin cycle	•
Emergency switch-off	•
Machine-independent accessories	•

Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Water recovery (optional)	•
LAN	•
WiFi	•
Connector Box	•

Capacities

Respirator masks [number]	26
Helmets [number]	10
Overalls [number]	6
Over jackets [number]	9
Chemical protection suits [number]	4
Synthetic duvets [number]	4
Synthetic pillows [number]	8
Down duvets [number]	4
Down pillows [number]	8
Cloths, 22 g [number]	800

PWM 935 [SI DV DD SOM]

Professional washing machine, steam heating (indirect)
for marine applications – freely programmable. 35 kg load size.



EAN: 4002516928492 / Material number: 12887750 /

Old Material Number: 51935008SOM

Cotton mops, 40 cm / 190 g [number]	184
Cotton mops, 50 cm / 220 g [number]	159
Microfibre mops, 40 cm / 120 g [number]	292
Microfibre mops, 50 cm / 170 g [number]	206
Summer horse blankets [number]	5

Standards, test certificates and symbols

CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•