

PLW 8683 CD [OIL DC5 CM]

Laboratory dishwasher

with liquid dispensing, DryPlus, conductivity monitoring & oil seals.



- Performance/cycle, e.g. 128 laboratory bottles
- Flexible and simple – modular load carriers & EasyLoad system
- Maximum user convenience with M Touch Flex full-touch colour display
- Safety through monitoring – wash pressure and spray arm monitoring
- Efficient hot air drying – DryPlus
- Connectivity as standard via WiFi

EAN: 4002516952381 / Material number: 12933450 /
Old Material Number: 6286C328GB

Construction type and version

Construction type	Freestanding, can be built-under, wide, with lid
Range	ExpertLine
Control panel colour	Black
Casing	Stainless steel
Can be built-under	•
Lid	Stainless Steel
Number of wash levels	2
AutoClose – automatic door lock	•
Buzzer, acoustic signal at end of programme	•
Service-friendly design	•

Application

Suitable for laboratories	•
---------------------------	---

Capacity

Narrow-necked glassware per cycle [number]	64
Test tubes per cycle [number]	196
Vials per cycle [number]	196
Laboratory flasks per cycle [number]	128
Pipettes per cycle [number]	98

Performance data

Circulation pump, Qmax in l/min	500
Wash cabinet usable capacity in l	145.00
Shortest programme running time in min	20
Tested operating hours	15000
Maximum final rinse temperature in °C	93

Miele MOVE

Miele MOVE Connect (option)	•
-----------------------------	---

Control system

Control type	M Touch Flex
Max. delay start in h	24
Programmability	programmable
Programmes [number]	20
Free programme positions [number]	10
Time left display	•
Programme sequence display	•
Selectable display languages	•

Standard electrical connection

Electrical connection	3N AC 400V 50HZ
Electric heater rating in kW	8.50
Total rated load in kW	9.30
Fuse rating in A	16
Length of mains connection cable in m	1.90

Possible voltage variant 1

Electrical connection	AC 230V 50HZ
Electric heater rating in kW	2.50
Total rated load in kW	3.30
Fuse rating in A	16

PLW 8683 CD [OIL DC5 CM]

Laboratory dishwasher

with liquid dispensing, DryPlus, conductivity monitoring & oil seals.



EAN: 4002516952381 / Material number: 12933450 /

Old Material Number: 6286C328GB

Water connection/drainage	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in kPa	200-1000
DI water [number]	1
Maximum delivery head for drain pump in cm	100
Maximum water hardness (cold water/hot water) in mmol/l	10.70
VEP feed pump for demineralised water (option)	•
Drain pump [DN]	22
Integrated water softener	•
Water protection system	Waterproof system
Drying unit	
Integrated drying unit	•
Fan in kW	0.30
Heater element in kW	2.20
Air throughput in m³/h	60
Time setting in 1-minute increments	0-120
HEPA filter class	H14
HEPA filter filtration efficiency (in accordance with DIN EN 1822) in %	99.99
HEPA filter service life in h	200
Dimensions and weight	
External dimensions, net height in mm	835
External dimensions, net width in mm	898
External dimensions, net depth in mm	700
External dimensions, gross height in mm	1095
External dimensions, gross width in mm	1200
External dimensions, gross depth in mm	800
Wash cabinet, usable height in mm	520
Wash cabinet, usable width in mm	530
Wash cabinet, depth of upper basket in mm	474
Net weight in kg	98
Wash cabinet, depth of lower basket in mm	520
Gross weight in kg	131
Maximum floor load in N/m²	1220
Emissions data	
Emission sound pressure level in the workplace	≤70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	4.32
Programmes	
Standard	•
Intensive	•
Extra short	•
Universal	•
Inorganic	•
Organic	•
Agar	•
Injector Plus	•
Pipettes	•
Plastics	•

PLW 8683 CD [OIL DC5 CM]

Laboratory dishwasher

with liquid dispensing, DryPlus, conductivity monitoring & oil seals.



EAN: 4002516952381 / Material number: 12933450 /

Old Material Number: 6286C328GB

Oil	•
Hygiene 93/10	•
Pasteurising	•
Cold water rinse	•
Demineralised water rinse	•
Features	
1 dispenser pump for liquid cleaning agent	•
1 dispenser pump for neutralising agent	•
Additional integrated dispensing pump 5–10 l (optional)	•
Suction lance for media canisters 10–20 l (optional)	•
Convenient suction lance DC5	•
Additional integrated dispenser pumps (optional)	•
Volume flow control	•
Steam condenser	•
Spray pressure monitoring	•
Spray arm monitoring	•
Conductivity monitoring	•
How-to sequences	•
Wash cabinet lighting	•
Interface for process documentation (optional)	•
Multi-component filter system	•
Variable-speed heater pump	•
Load carrier – direct coupling	•
DryPlus	•
In-door salt container	•
Customer Service optical interface	•
Setting options for process chemicals (3 x 5 l / 2 x 10 l)	•
Wash cabinet seamlessly welded using laser technology	•
Heater elements outside wash cabinet	•
EasyLoad	•
Oil and grease-resistant seals	•
Wash cabinet made from high-quality stainless steel (1.4301/304)	•
Extensive components (option)	•
Connection options	
WiFi	•
Ethernet interface (optional)	•
Standards, test certificates and symbols	
CE	•
VDE (electrical safety)	•
IP safety class according to EN 60529: IP 21	•
EN 61010-1	•
EN 61010-2-040	•
RoHS guideline 2011/65/EU	•
Regulation 4 compliant	•
Machinery Directive 2006/42/EC	•
KIWA certificate for water safety	•