

KFN 4898 A-20 D

Freestanding fridge-freezer

for lasting freshness and convenience with PerfectFresh Active and Freeze&Cool.



- Super efficient A-20 %: 20 % more economical than energy efficiency class A
- Fresh 5 x longer with active humidification – PerfectFresh Active
- Flexible use of freezer – Freeze&Cool
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- Handleless appliances are easy to open thanks to Click2open
- No icing up of food and no need to defrost thanks to NoFrost



EAN: 4002516979210 / Material number: 12993630 /

Old Material Number: 38489842EU1

General information	
Model identifier	KFN 4898 A-20 D
Manufacturer material number	12993630
EAN number	4002516979210
Marketing class	Platinum
Appliance category	
Fridge-freezer	•
Construction type	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Casing colour	BlackSteel
Front colour	BlackSteel
Freezer compartment lighting	LED
Fan lighting	•
Freshness system lighting	•
User convenience	
Fridge zone lighting	FlexiLight 2.0
Networking with Miele@home	•
Freshness system	PerfectFresh Active
Door opening aid	Click2open
Freeze & Cool	•
Fine adjustment inner door	•
ComfortClean	•
ComfortSize	•
DynaCool	•
NoFrost	•
DuplexCool	•
VarioRoom	•
SoftClose	•
SelfClose	•
Smart Extras	
Push notifications	•
Cooling tips	•
Cooling modes	•
Smart Extras	
RemoteUpdate	•
Smart Home Integration	•
Control system	
Operating concept	FreshTouch
Precise adjustment	Fridge and freezer temperature
Fridge compartment can be switched off	•
Freezer section, can be deactivated	•
Independent temperature regulation of fridge and freezer zones	•
SuperCool	•

KFN 4898 A-20 D

Freestanding fridge-freezer

for lasting freshness and convenience with PerfectFresh Active and Freeze&Cool.



EAN: 4002516979210 / Material number: 12993630 /

Old Material Number: 38489842EU1

SuperFreeze	•
No. of temperature zones	3
Sabbath mode	•
Party mode	•
Holiday mode	•
Fridge/Fridge section	
No. of shelves	4
including number of split shelves (FlexiBoard)	1
of which illuminated	2
Chrome-plated metal bottle rack	•
No. of crisper drawers	2
Dry back wall	CleanSteel
Number of inner door racks for tinned food	2
Door rack for bottles	1
Door shelves	3
Freezer/Freezer section	
Number of freezer drawers	3
Efficiency	
Energy efficiency class (A–G)	A
Annual energy consumption in kWh	92.35
Energy consumption in 24 h in kWh	0.25
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
Technical data	
Appliance width in mm	597
Appliance height in mm	2015
Appliance depth in mm	675
Weight in kg	108.1
Climate class	SN-T
Refrigerator compartment in l	259
including PerfectFresh zone in l	99
4* freezer compartment in l	103
Total usable capacity in l	362
Storage time in case of fault in h	24
Freezer capacity in kg/24 h	10.00
Acoustic airborne noise emission class (A–D)	A
Sound emissions in dB(A) re 1 pW	29
Current consumption (mA)	1400
Voltage in V	220 - 240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50 - 60
Length of supply lead in m	2.0

KFN 4898 A-20 D
Freestanding fridge-freezer
for lasting freshness and convenience with PerfectFresh Active and Freeze&Cool.




EAN: 4002516979210 / Material number: 12993630 /
Old Material Number: 38489842EU1

Replacing lamps	Service
Accessories included	
Egg tray	•
PerfectFresh organisation box	•
Ice cube tray	•

KFN 4898 A-20 D


Freestanding fridge-freezer

for lasting freshness and convenience with PerfectFresh Active and Freeze&Cool.




KFN4898AD bs, KFN4898CD bs, installation sketch

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4898CD bs, KFN4898AD bs, KS4887DD edt/cs, top view

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4395DD, KFN4393CD, KFN4393FD, KFN4393DD, KFN4795DD bb, KFN4795CD bb, KFN4898CD, installation

1. View from the front, 2. Mains connection cable, L = 2000 mm