

G 7281 SCVi

Fully integrated dishwashers

A -20 %* | 43 dB | Cutlery tray | ExtraComfort baskets | QuickPowerWash | AutoOpen



- Tested for the equivalent of 20 years' service life*
- Best energy efficiency class A – energy-saving and eco-friendly
- Convenient, great results and perfect for everyday use – ExtraComfort baskets
- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- Perfect results in less than one hour – QuickPowerWash
- Completely dry – Miele AutoOpen drying

* During the development phase of the G 5000 and G 7000 dishwasher series, Miele tested models and core components in 5600 wash cycles (= 280 wash cycles per year over a period of 20 years) in various programmes. More at: miele.com/20years



EAN: 4002517051403 / Material number: 13184010 / Old Material Number: 21728162GB

General information

Model identifier	G 7281 SCVi
Manufacturer material number	13184010
EAN number	4002517051403
Marketing class	Gold

Model

Fully integrated dishwasher	•
60 cm dishwasher	•

Design

Control panel colour	Stainless Steel.
Control panel version	Fully integrated fascia
Control type	Programme selector buttons
Display	1-line clear text display
Display colour	White
MultiLingua	•

Convenience

Door closing aid	ComfortClose
Time left display	•
Delay start up to 24 hours	•
In-operation indicator	optical and acoustic
Display language selection	•

Efficiency

Energy efficiency class (A–G)	A
Water consumption in the Automatic programme in l from	6.0
Water consumption of the ECO programme in litres per programme cycle	8.2
Electricity consumption in the ECO programme in kWh	0.43
Energy consumption of the ECO programme in kWh after 100 programme cycles	43
Consumption value in kWh in the ECO programme with hot water connection	0.30
Duration of ECO programme in minutes	388
Power rating with delay start in W	0.30
Power rating in off mode in W	0.30
Power rating in standby mode in W	0.30
Number of place settings	14
Noise emission class	B
Noise emissions in dB(A)	42
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•

Quality of results

Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•

G 7281 SCVi

Fully integrated dishwashers

A -20 %* | 43 dB | Cutlery tray | ExtraComfort baskets | QuickPowerWash | AutoOpen



EAN: 4002517051403 / Material number: 13184010 / Old Material Number: 21728162GB

Water softener system

Uni. water softener to 70° dH, Economic salt consumption, Brilliant GlassCare

Active condensation drying

•

BrilliantGlassCare

•

Wash programmes

QuickPowerWash

•

ECO

•

Automatic

•

ComfortWash 45 °C

•

Intensive 75 °C

•

PowerWash

•

ComfortWash+ 55 °C

•

Gentle

•

ExtraQuiet 39 dB(A)

•

Appliance care

•

Rinse out salt

•

Dishwashing options

BottleClean

•

Quick

•

IntenseZone

•

Extra Clean

•

Extra dry

•

Basket design

Cutlery loading

3D MultiFlex tray

FlexCare glass holder

2

FlexCare cup rack

1

Basket design

ExtraComfort

MultiClip

•

FlexCare Glass & Bottle

•

XL Assist

•

Safety

Waterproof system

•

Filter indicator light

•

Hygiene info

•

Technical data

Niche width minimal in mm

600

Niche width max in mm

600

Niche height minimal in mm

805

Niche height maximal in mm

870

Niche depth in mm

550

Depth with door open in cm

116.5

Net weight in kg

48.0

Total rated load in kW

2.00

Voltage in V

230

Fuse rating in A

10

Number of phases

1

Electrical frequency standard

50

G 7281 SCVi
Fully integrated dishwashers
A -20 %* | 43 dB | Cutlery tray | ExtraComfort baskets | QuickPowerWash | AutoOpen



EAN: 4002517051403 / Material number: 13184010 / Old Material Number: 21728162GB

Length of water inlet hose in m	1.50
Length of water drain hose in m	1.50
Length of supply lead in m	1.80
Min. front panel weight in kg	4.0
Max. front panel weight in kg	10.0
[can be retrofitted by Service to min.]	8.0
[can be retrofitted by Service to max.]	16.0

Accessories included	
----------------------	--

Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price	•
--	---


Available display languages	
-----------------------------	--

Available display languages via MultiLingua	□□□□□□□, deutsch, english (AU), english (GB), □□□, □□□
---	--

G 7281 SCVi

Fully integrated dishwashers

A -20 %* | 43 dB | Cutlery tray | ExtraComfort baskets | QuickPowerWash | AutoOpen



G7000, fully integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),