

FG 40
Chassis
with four castors, suitable for laundry tub WW 45.



- Suitable for Miele Professional laundry tub WW 45
- Height 29.2 (loading height), width 55, depth 36 cm

EAN: 4002511097810 / Material number: 02101810 / Old Material Number: 59120007D

Product classification	
Washing machines	•
Tumble dryers	•
Ironers	•
Machine/accessory category	
HM 16-80	•
HM 16-83	•
PM 1210	•
PM 1214	•
PM 1217	•
PM 1318	•
PM 1418	•
PM 1421	•
D 500-2000	•
D 500-2200	•
D 500-2500	•
D 500-3000	•
D 500-3300	•
D 600-1750	•
D 600-2000	•
D 600-2200	•
D 600-2500	•
D 600-3000	•
D 600-3300	•
D 800-1300	•
D 800-1750	•
D 800-2000	•
D 800-2200	•
D 800-2500	•
D 800-3000	•
D 800-3300	•
M 500-1750	•
M 500-2000	•
M 500-2200	•
M 500-2500	•
M 500-3000	•
M 500-3300	•
PM 1621	•
PM 1625	•
PM 1630	•
PM 1635	•
PM 1825	•
PM 1830	•
PM 1835	•
PT 5135 C	•
PT 5136	•
PT 5137 WP	•
PT 5140 WP	•
PT 5145 C	•
PT 5186	•

FG 40
Chassis
with four castors, suitable for laundry tub WW 45.



EAN: 4002511097810 / Material number: 02101810 / Old Material Number: 59120007D

PT 7186	•
PT 7188	•
PT 7135 C	•
PT 7136	•
PT 7137 WP	•
PT 8203	•
PT 8251	•
PT 8251 COP	•
PT 8253	•
PT 8257	•
PT 8257 WP	•
PT 8301	•
PT 8301 COP	•
PT 8303	•
PT 8331	•
PT 8331 COP	•
PT 8333	•
PT 8333 HW	•
PT 8337	•
PT 8337 HW	•
PT 8337 WP	•
PT 8401	•
PT 8403	•
PT 8403 HW	•
PT 8407	•
PT 8407 HW	•
PT 8503	•
PT 8503 HW	•
PT 8507	•
PT 8507 HW	•
PT 8803	•
PT 8803 HW	•
PT 8807	•
PT 8807 HW	•
PW 413	•
PW 418	•
PW 5064	•
PW 5062	•
PW 5065	•
PW 5064 MOPSTAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOPSTAR 80	•
PW 5104 MOPSTAR 100	•
PW 5105 Vario	•
PW 5134 MOPSTAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•

FG 40
Chassis
with four castors, suitable for laundry tub WW 45.



EAN: 4002511097810 / Material number: 02101810 / Old Material Number: 59120007D

PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PWT 6089	•
PW 200 Profi@Work	•
PT 200 Profi@Work	•
Product category	
Storage/transport system	•
Product properties	
Electrical connection	OHNE
Colour	Octoblue
Dimensions and weight	
External dimensions, net height in mm	292
External dimensions, net width in mm	550
External dimensions, net depth in mm	360
External dimensions, gross height in mm	340
External dimensions, gross width in mm	560
External dimensions, gross depth in mm	370
Net weight [kg]	7.50
Gross weight in kg	7.50