

E 385  
Mobile unit  
for the optimum loading of narrow necked glassware.



- equipped with 16 injector nozzles
- Equipped with connection for hot air drying
- Bracket for ML/2 for mobile unit recognition / spray arm control

EAN: 4002511116511 / Material number: 03809930 / Old Material Number: 69538501D

<b>Product category</b>	
Washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PG 8535	•
PG 8536	•
<b>Product category</b>	
Mobile unit with connection for hot-air drying	•
Mobile unit for narrow-necked glassware	•
<b>Product properties</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
<b>Area of application</b>	
Reprocessing of laboratory glassware	•
<b>Capacity</b>	
Narrow-necked glassware [number]	16
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	502
External dimensions, net width in mm	535
External dimensions, net depth in mm	517
External dimensions, gross height in mm	550
External dimensions, gross width in mm	540
External dimensions, gross depth in mm	280
Net weight in kg	5.70
Gross weight in kg	6.70
<b>Companion pack</b>	
E 351 injector nozzle, Ø 4 mm, length 160 mm [number]	7
E 352 injector nozzle, Ø 6 mm, length 220 mm [number]	9
E 353 clip for injector nozzle E 351 [number]	7
E 354 clip for injector nozzle E 352 [number]	9
Rinse nozzle for powder dispenser [number]	1