

E 314

Tap fitting

for the manual production of demineralised water.



- Pressurised to 10 bar
- Pressure-proof to 10 bar
- Including Pressure hose 150 cm
- Complete with pressure hose 150 cm

EAN: 4002511115286 / Material number: 03830340 / Old Material Number: 69431401D

Product category	
Fresh-water dishwashers	•
Throughfeed tank dishwashers	•
Washer-disinfectors, laboratory	•
Machine affiliation	
G 8066	•
PG 8067	•
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8063	•
PG 8164	•
PG 8165	•
PG 8166	•
PG 8169	•
PG 8172	•
PG 8172 Eco	•
PTD 901	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
PTD 701	•
PTD 702	•

E 314

Tap fitting

for the manual production of demineralised water.



EAN: 4002511115286 / Material number: 03830340 / Old Material Number: 69431401D

PTD 703	•
PTD 704	•
PG 8535	•
PG 8536	•
Product category	
Water treatment	•
Other accessories	•
Product properties	
Material	Plastic
Colour	Black
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	0
External dimensions, net width in mm	0
External dimensions, net depth in mm	0
External dimensions, gross height in mm	135
External dimensions, gross width in mm	420
External dimensions, gross depth in mm	210
Net weight in kg	1.70
Gross weight in kg	1.81