

E 315

Full demineralisation single use resin

For the regeneration of full demineralisation cartridges

EAN: 4002511115293 / Material number: 03830350 / Old Material Number: 69431501D



- 20 l of homogenously mixed resins
- For use in the LP 2800 empty cartridge
- Carton with 2 bags at 10 litres
- Vacuum sealed in plastic bags
- Including filter bag for exchange

Product category	
Fresh-water dishwashers	•
Tank dishwashers	•
Throughfeed tank dishwashers	•
Washer-disinfectors, laboratory	•
Thermal disinfectors	•
Washer-disinfectors, medical	•
Machine affiliation	
G 8066	•
PG 8067	•
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8063	•
PG 8164	•
PG 8165	•
PG 8166	•
PG 8169	•
PG 8172	•
PG 8172 Eco	•
PTD 901	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•

E 315

Full demineralisation single use resin

For the regeneration of full demineralisation cartridges

EAN: 4002511115293 / Material number: 03830350 / Old Material Number: 69431501D



PFD 408 U	•
PTD 701	•
PTD 702	•
PTD 703	•
PTD 704	•
PG 8581	•
PG 8582	•
PG 8583	•
PG 8583 CD	•
PG 8591	•
PG 8592	•
PG 8593	•
<b>Product category</b>	
Water treatment	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0.00-0.00
Fuse rating in A	0-0
<b>Dimensions and weight</b>	
External dimensions, gross height in mm	130
External dimensions, gross width in mm	400
External dimensions, gross depth in mm	550
Net weight in kg	13.58
Gross weight in kg	14.21