

E 809

Lower basket insert, plastic coated

For the optimum loading of cups.



- Suitable for lower basket U 881
- For 23 cups with a diameter of max. 9 cm

EAN: 4002512259453 / Material number: 05018650 / Old Material Number: 67580901D

| Product classification | |
|--------------------------------|---------------------|
| Fresh-water dishwashers | • |
| Machine affiliation | |
| PG 8041 | • |
| PG 8043 | • |
| PG 8045 | • |
| PG 8055 | • |
| PG 8055 U | • |
| PG 8056 | • |
| PG 8056 U | • |
| PG 8057 TD | • |
| PG 8057 TD U | • |
| PG 8058 | • |
| PG 8058 U | • |
| PG 8059 | • |
| PG 8059 U | • |
| PG 8060 | • |
| PG 8061 | • |
| PG 8061 U | • |
| PG 8096 | • |
| PG 8096 U | • |
| PG 8099 | • |
| PG 8099 U | • |
| PFD 400 | • |
| PFD 400 U | • |
| PFD 401 | • |
| PFD 401 U | • |
| PFD 402 | • |
| PFD 402 U | • |
| PFD 404 | • |
| PFD 404 U | • |
| PFD 405 | • |
| PFD 405 U | • |
| PFD 407 | • |
| PFD 407 U | • |
| PFD 408 U | • |
| Product category | |
| Attachment for cups | • |
| Product properties | |
| Material | Wire, rilsan-coated |
| Colour | White |
| For use in lower basket | U 881 |
| Capacity | |
| Cups [number] | 23 |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |

E 809

Lower basket insert, plastic coated
For the optimum loading of cups.

EAN: 4002512259453 / Material number: 05018650 / Old Material Number: 67580901D



| Dimensions and weight | |
|---|------|
| External dimensions, net height in mm | 71 |
| External dimensions, net width in mm | 506 |
| External dimensions, net depth in mm | 495 |
| External dimensions, gross height in mm | 530 |
| External dimensions, gross width in mm | 545 |
| External dimensions, gross depth in mm | 110 |
| Net weight in kg | 2.20 |
| Gross weight in kg | 3.60 |