


A 9/1

Perforated tray inlay

For the gentle cleaning of delicate items by interrupting the spray jet.



- 7 x 7 mm perforation, 3 mm slat

EAN: 4002513531176 / Material number: 06097010 / Old Material Number: 69500902D

| | |
|--|-----------------|
| Product category | |
| Large-capacity washer-disinfectors, laboratory | • |
| Machine affiliation | |
| PG 8527 | • |
| Product category | |
| Underlay | • |
| Product properties | |
| Material | Stainless steel |
| Colour | Stainless Steel |
| Area of application | |
| Reprocessing of laboratory glassware | • |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0.00 |
| Fuse rating in A | 0 |
| Dimensions and weight | |
| External dimensions, net height in mm | 1 |
| External dimensions, net width in mm | 773 |
| External dimensions, net depth in mm | 573 |
| External dimensions, gross height in mm | 10 |
| External dimensions, gross width in mm | 870 |
| External dimensions, gross depth in mm | 590 |
| Net weight in kg | 1.70 |
| Gross weight in kg | 1.80 |