

E 474/4

Basic mobile unit

for optimum loading of up to 2 MIS sets in a modular system.



- For hollow instruments in 3 insert modules
- Equipped with connection for hot air drying
- For: E 903, E 905, E 906, E 444, E 460, E 457, E 142
- Bracket for ML/2 for mobile unit recognition / spray arm control

EAN: 4002513805536 / Material number: 06439160 / Old Material Number: 69547405D

Product category	
Washer-disinfectors, medical	•
Machine affiliation	
PG 8536	•
Product category	
Mobile unit for MIS instruments	•
Product properties	
Material	Stainless steel
Colour	Stainless Steel
Area of application	
Reprocessing of MIS instruments	•
Reprocessing of dental instruments	•
Capacity	
MIS sets [number]	2
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	507
External dimensions, net width in mm	535
External dimensions, net depth in mm	515
External dimensions, gross height in mm	540
External dimensions, gross width in mm	540
External dimensions, gross depth in mm	630
Net weight in kg	10.17
Gross weight in kg	10.17
Companion pack	
E 362 blind stopper [number]	2
E 447 female adapter, for male Luer Lock [number]	3