

Printer
Report printer
for process documentation, integrated



- 8-wire matrix printer for process documentation
- Report creation and printing can be configured
- Can be installed on the operator side of the PG 8527
- Can be installed on the clean or unclean side of the PG 8528

EAN: 4002514111766 / Material number: 06758340 / Old Material Number: 69247001D

| Product category | |
|--|-----------|
| Large-capacity washer-disinfectors, laboratory | • |
| Large-capacity washer-disinfectors, medical | • |
| Machine affiliation | |
| PG 8527 | • |
| PG 8528 | • |
| Product category | |
| Other accessories | • |
| Standard electrical connection | |
| Number of phases | 1 |
| Neutral conductor | N |
| AC/DC | AC |
| Voltage in V | 220-240 |
| Frequency in Hz | 50-60 |
| Total rated load in kW | 0.00-0.00 |
| Fuse rating in A | 0-0 |
| Dimensions and weight | |
| External dimensions, gross height in mm | 305 |
| External dimensions, gross width in mm | 300 |
| External dimensions, gross depth in mm | 200 |
| Net weight in kg | 0.90 |
| Gross weight in kg | 1.00 |