


CS 1112 E
ProLine element
with two electrically heated cooking zones




- Professional design – ceramic glass with frame measuring 288 mm 288 mm wide
- Very convenient, safe – operating and residual heat indicator
- Easy and direct controls -operation via metal rotary dial control
- Particularly versatile – 2 cooking zones incl. 1 Vario zone

EAN: 4002514407388 / Material number: 07131020 / Old Material Number: 27111250GB

Heating type	
Heating type	Electric
Construction type	
ProLine	•
Design	
Elegant glass ceramic surface	•
Stainless steel frame	•
Print design	LightPrint
Miele logo embossed in stainless steel	•
Surface-mounted installation	•
Cooking zone details	
Number of cooking zones	2
1st cooking zone/cooking area	
Position	front centre
Type	Single-circuit ring
Size in mm	Ø 145
Max. rating in W	1200
2nd cooking zone/cooking area	
Position	rear centre
Type	Dual-circuit ring
Size in mm	Ø 100-180
Max. rating in W	700/1800
User convenience	
Extended cooking zone	•
Operation via knobs	•
Cleaning and care	
Easy to clean ceramic glass	•
Safety	
Safety switch-off	•
Overheating protection	•
Residual heat indicator	•
Operational indicator	•
Technical data	
Dimensions (H x W x D) in mm	73 x 288 x 520
Dimensions in mm (width)	288
Dimensions in mm (height)	73
Dimensions in mm (depth)	520
Cutout dimensions in mm (width) with surface-mounted installation	272
Cutout dimensions in mm (depth) with surface-mounted installation	500
Casing height incl. connection box in mm	95
Weight in kg	7
Total rated load in kW	3.00
Length of supply lead in m	1.4
Voltage in V	220-240
Frequency in Hz	50-60
Accessories included	
Razor-blade scraper	•
Mains cable	Yes

CS 1112 E
ProLine element
with two electrically heated cooking zones



CS1112E/CS1212I (Installation drawing)

Installation note: This unit should only be installed above a built-in oven if the latter has an integrated cooling fan.,
Heart pacemaker: When the unit is in operation, the area immediately surrounding the unit is electromagnetically charged., Under certain conditions, this could affect the proper functioning of pacemaker: If in any doubt, please consult the manufacturer of the pacemaker or your health care professional., 1) Front, 2) Height for building in, 3) Mains connection box with cable, 2000 mm long