

E 909

Mobile unit

for the ideal loading of up to 1-2 MIS sets and mesh trays in a modular system.



- Levels 1-3 free for mesh trays, e.g. E 142
- The loading areas for the individual levels are different
- Equipped with connection for hot air drying
- Magnetic strip for mobile unit recognition (incl. magnets ML)

EAN: 4002514432809 / Material number: 07201500 / Old Material Number: 69590901D

Product classification	
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
PG 8527	•
PG 8528	•
Product category	
Mobile unit with connection for hot-air drying	•
Mobile unit for MIS instruments	•
Product properties	
Material	Stainless steel
Colour	Stainless Steel
Area of application	
Reprocessing of MIS instruments	•
Capacity	
DIN mesh trays [number]	9
SPRI mesh trays [number]	3
MIS sets [number]	1-2
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	698
External dimensions, net width in mm	640
External dimensions, net depth in mm	790
External dimensions, gross height in mm	720
External dimensions, gross width in mm	830
External dimensions, gross depth in mm	780
Net weight in kg	26.50
Gross weight in kg	30.00
Companion pack	
Magnetic strip for automatic mobile unit recognition (incl. magnets) [number]	1