

B 995 D

Rotary ironer

with steam function for optimum results and even more convenience.



- No physical effort required thanks to high pressure
- Convenient ironing of large laundry pieces – wide heater plate
- Individual work speed thanks to variable roller speed
- Iron difficult laundry items easily – all-round free roller end
- Best result even with dry textiles – Steam function

EAN: 4002514443706 / Material number: 07222770 / Old Material Number: 13099506GB

<b>Design</b>	
Colour	Lotus white
<b>Perfect ironing results</b>	
Temperature selection to suit textiles	•
High contact pressure (N/cm <sup>2</sup> )	0.35
Laundry feed board for easy laundry feed	•
Convenient infeed board with ample storage space	•
Airing bar for crease-free cooling	•
Steam function	•
Steam generator capacity in l	0.84
Dual-tank technology	•
Uses tap water	•
<b>Time-saving ironing</b>	
Roller length in mm	830
Variable roller speed	•
Moisture-absorbing roller padding	•
<b>User convenience</b>	
Effortless ironing while seated possible	•
Free roller end	•
Clear control panel	•
Convenient folding mechanism	•
Easily manoeuvrable thanks to four castors	•
<b>Safety</b>	
Automatic finger guard	•
Emergency release	•
Good stability	•
<b>Technical data</b>	
Dimensions in mm (width)	985
Dimensions in mm (height)	959
Dimensions in mm (depth)	380
Dimensions in mm (width), folded	500
Dimensions in mm (height), folded	1055
Dimensions in mm (depth), folded	380
Total rated load in kW	3.00
Frequency in Hz	50-60
<b>Accessories included</b>	
Adhesive film for temperature selector	•
Funnel for water container	•