

E 440/3

Mobile unit

for optimum cleaning of micro instruments (eye OP), for 4 OP sets.



- With integrated magnetic spray arm
- Levels 1 + 2 e.g. 4 x E 441/1 or 2 x E 142 per level
- Level 3 left: 20 connections for hollow instruments
- Level 3 right: 16 Luer lock adapters, male, horizontal Hose
- Bracket for ML/2 for mobile unit recognition / spray arm control

EAN: 4002514556260 / Material number: 07333140 / Old Material Number: 69544004D

<b>Product category</b>	
Washer-disinfectors, medical	•
<b>Machine affiliation</b>	
PG 8536	•
<b>Product category</b>	
Mobile unit for ophthalmology instruments	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Area of application</b>	
Reprocessing of ophthalmology instruments	•
<b>Capacity</b>	
Theatre sets for micro instruments [number]	4
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	502
External dimensions, net width in mm	535
External dimensions, net depth in mm	515
External dimensions, gross height in mm	540
External dimensions, gross width in mm	270
External dimensions, gross depth in mm	525
Net weight in kg	2.40
Gross weight in kg	3.30
<b>Companion pack</b>	
E 476 holder [number]	1
E 477 stopper [number]	1
E 790 Luer Lock connection element female to female [number]	8
E 791 Luer Lock connection element female to male [number]	8