

E 936

Insert

for optimum loading of up to 15 lamp handles.



EAN: 4002514811260 / Material number: 07759480 / Old Material Number: 69593601D

<b>Product category</b>	
Large-capacity washer-disinfectors, medical	•
<b>Machine affiliation</b>	
G 7823	•
G 7824	•
G 7826	•
PG 8527	•
PG 8528	•
<b>Product category</b>	
Other inserts	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Area of application</b>	
Reprocessing of surgical instruments	•
<b>Capacity</b>	
Lamp handles [number]	15
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	90
External dimensions, net width in mm	245
External dimensions, net depth in mm	500
External dimensions, gross height in mm	130
External dimensions, gross width in mm	275
External dimensions, gross depth in mm	530
Net weight in kg	0.50
Gross weight in kg	0.92