

WW 85 B
Laundry tub, blue
with 85 l capacity.



- Suitable for FG 85
- Height (incl. handles) 34.5, width 80, depth 54 cm

EAN: 4002515031278 / Material number: 09121090 / Old Material Number: 59100009D

| Product classification | |
|----------------------------|---|
| Washing machines | • |
| Tumble dryers | • |
| Ironers | • |
| Drying cabinets | • |
| Machine/accessory category | |
| HM 16-80 | • |
| HM 16-83 | • |
| PM 1210 | • |
| PM 1214 | • |
| PM 1217 | • |
| PM 1318 | • |
| PM 1418 | • |
| PM 1421 | • |
| PRI 318 | • |
| PRI 418 | • |
| D 500-1750 | • |
| D 500-2000 | • |
| D 500-2200 | • |
| D 500-2500 | • |
| D 500-3000 | • |
| D 500-3300 | • |
| D 600-1750 | • |
| D 600-2000 | • |
| D 600-2200 | • |
| D 600-2500 | • |
| D 600-3000 | • |
| D 600-3300 | • |
| D 800-1300 | • |
| D 800-1750 | • |
| D 800-2000 | • |
| D 800-2200 | • |
| D 800-2500 | • |
| D 800-3000 | • |
| D 800-3300 | • |
| M 500-1750 | • |
| M 500-2000 | • |
| M 500-2200 | • |
| M 500-2500 | • |
| M 500-3000 | • |
| M 500-3300 | • |
| PM 1621 | • |
| PM 1625 | • |
| PM 1630 | • |
| PM 1635 | • |
| PM 1825 | • |
| PM 1830 | • |
| PM 1835 | • |
| PT 5135 C | • |
| PT 5136 | • |

WW 85 B
Laundry tub, blue
with 85 l capacity.



EAN: 4002515031278 / Material number: 09121090 / Old Material Number: 59100009D

| | |
|---------------------|---|
| PT 5137 WP | • |
| PT 5140 WP | • |
| PT 5141 WP | • |
| PT 5145 C | • |
| PT 5155 C | • |
| PT 5156 | • |
| PT 5157 WP | • |
| PT 5186 | • |
| PT 7186 | • |
| PT 7188 | • |
| PT 7135 C | • |
| PT 7136 | • |
| PT 7137 WP | • |
| PT 7138 | • |
| PT 8203 | • |
| PT 8251 | • |
| PT 8251 COP | • |
| PT 8253 | • |
| PT 8257 | • |
| PT 8257 WP | • |
| PT 8301 | • |
| PT 8301 COP | • |
| PT 8303 | • |
| PT 8331 | • |
| PT 8331 COP | • |
| PT 8333 | • |
| PT 8333 HW | • |
| PT 8337 | • |
| PT 8337 HW | • |
| PT 8337 WP | • |
| PT 8401 | • |
| PT 8403 | • |
| PT 8403 HW | • |
| PT 8407 | • |
| PT 8407 HW | • |
| PT 8503 | • |
| PT 8503 HW | • |
| PT 8507 | • |
| PT 8507 HW | • |
| PT 8803 | • |
| PT 8803 HW | • |
| PT 8807 | • |
| PT 8807 HW | • |
| PT 9136 | • |
| PT 9137 WP | • |
| PW 413 | • |
| PW 413 Mop Star 130 | • |
| PW 418 | • |
| PW 5064 | • |
| PW 5062 | • |
| PW 5055 | • |

WW 85 B
Laundry tub, blue
with 85 l capacity.

EAN: 4002515031278 / Material number: 09121090 / Old Material Number: 59100009D

| | |
|---------------------|---|
| PW 5065 | • |
| PW 5064 MOPSTAR 60 | • |
| PW 5070 | • |
| PW 5082 | • |
| PW 5084 MOPSTAR 80 | • |
| PW 5104 MOPSTAR 100 | • |
| PW 5105 Vario | • |
| PW 5134 MOPSTAR 130 | • |
| PW 6055 | • |
| PW 6065 | • |
| PW 6055 Vario | • |
| PW 6065 Vario | • |
| PW 6065 Plus | • |
| PW 6068 Plus | • |
| PW 6080 | • |
| PW 6088 | • |
| PW 6107 | • |
| PW 6137 | • |
| PW 5136 | • |
| PW 6163 | • |
| PW 6167 | • |
| PW 6207 | • |
| PW 6241 | • |
| PW 6243 | • |
| PW 6321 | • |
| PW 6323 | • |
| PW 811 | • |
| PW 814 | • |
| PW 818 | • |
| PW 9055 | • |
| PW 9065 | • |
| PWT 6089 | • |
| PWM 500-08 | • |
| PWM 500-09 | • |
| PWM 506 Mop Star 60 | • |
| PWM 507 | • |
| PWM 508 Mop Star 80 | • |
| PWM 900-09 | • |
| PWM 906 | • |
| PWM 907 | • |
| PWM 908 | • |
| PW 200 Profi@Work | • |
| PT 200 Profi@Work | • |
| PDR 300 SmartBiz | • |
| PWM 300 SmartBiz | • |
| PDR 500-08 | • |
| PDR 507 | • |
| PDR 900-08 | • |
| PDR 908 | • |
| PIB 100 | • |

WW 85 B
Laundry tub, blue
with 85 l capacity.



EAN: 4002515031278 / Material number: 09121090 / Old Material Number: 59100009D

| Product category | |
|---|---------|
| Storage/transport system | • |
| Product properties | |
| Electrical connection | OHNE |
| Material | Plastic |
| Colour | Blue |
| Volume in l | 85 |
| Dimensions and weight | |
| External dimensions, net height in mm | 300 |
| External dimensions, net width in mm | 800 |
| External dimensions, net depth in mm | 550 |
| External dimensions, gross height in mm | 340 |
| External dimensions, gross width in mm | 800 |
| External dimensions, gross depth in mm | 550 |
| Net weight [kg] | 2.75 |
| Gross weight in kg | 3.00 |