

KM 2354

Gas hob

in maximum width for the ultimate in cooking and user convenience.



- Simple controls -single-handed operation via rotary dial control
- Modern design – 888 mm wide, flat-fit stainless-steel trough
- Particularly versatile – 5 burners incl. 1 dual wok
- Extremely safe – GasStop function
- Easy cleaning – dishwasher-safe ComfortClean pot rests

EAN: 4002515169032 / Material number: 09289880 /
Old Material Number: 26235450GB

General information	
Model identifier	KM 2354
Manufacturer material number	09289880
EAN number	4002515169032
Marketing class	Platinum
Heating type	
Heating type	Gas
Construction type	
Independent of cooker	•
Design	
Miele logo embossed in stainless steel	•
Cast iron pot rests (matt black enamelled)	•
Cooking zone details	
Number of cooking zones	5
Gas burner power rating	
Small burner in kW	1.00
Medium burner in kW	1.70
Large burner in kW	2.70
Dual wok burner in kW	4.50
1st cooking zone/cooking area	
Position	front left
Type	Economy burner
2nd cooking zone/cooking area	
Position	rear left
Type	High-speed burner
3rd cooking zone/cooking area	
Position	Centred
Type	Dual wok burner
4th cooking zone/cooking area	
Position	rear right
Type	Standard burner
5th cooking zone/cooking area	
Position	front right
Type	Standard burner
User convenience	
Operation via knobs	•
Electronic ignition with single-hand operation	•
Cleaning and care	
Dishwasher-proof pot rests	•
Safety	
GasStop	•
Technical data	
Dimensions (H x W x D) in mm	75 x 888 x 508
Dimensions in mm (width)	888
Dimensions in mm (height)	75
Dimensions in mm (depth)	508
Casing height incl. connection box in mm	90

KM 2354

Gas hob

in maximum width for the ultimate in cooking and user convenience.




EAN: 4002515169032 / Material number: 09289880 /
Old Material Number: 26235450GB

Cutout dimensions in mm (width) with surface-mounted installation	862 mm
Cutout dimensions in mm (depth) with surface-mounted installation	490 mm
Weight in kg	19
Total rated load in kW	11.60
Length of supply lead in m	1.4
Position of gas connection	Hinten links
Voltage in V	220-240
Frequency in Hz	50-60
Accessories included	
Mains cable	Yes
Wok ring	•
Small trivet	•

KM 2354

Gas hob

in maximum width for the ultimate in cooking and user convenience.



KM 2354 (Skizze)

1. front, 2. Building-in depth, 3. Gas connection R 1/2 - ISO 7-1 (DIN EN 10226), 4. Mains connection box with mains connection cable L = 2000 mm