

M 6012 SC

Freestanding microwave oven
with knob controls on the side at an attractive entry-level price.



- Perfect defrosting and cooking – Automatic programmes
- Optimum and even browning – integrated Quartz grill
- Multi-stage cooking processes in just one step – Memory function
- Very powerful microwave – 900 W
- Compact – 26 l oven compartment volume

EAN: 4002515275252 / Material number: 09546480 / Old Material Number: 24601250GB

Construction type and design	
Countertop microwave oven	•
Colour	Stainless steel
SideControl	•
Convenience features	
Keeping warm	•
Quartz grill	•
Operating modes	
Automatic programmes	•
Grill	•
Microwave solo operation	•
Microwave/grill combination mode	•
User convenience	
Display	EasyControl
Time of day display	•
Minute minder	•
Programmable cooking duration	•
Quick microwave	•
Memory function	•
Individual settings	•
Efficiency and sustainability	
Night dimming	•
Cleaning and care	
Stainless steel oven compartment	•
Safety	
Appliance cooling system and touch-cool front	•
System lock	•
Safety switch-off	•
Safety lock "Door" warning	•
Technical data	
Oven compartment volume in l	26
Door hinge	Left
Oven light	1 LED spot
Oven interior height in cm	20.7
Turntable diameter in cm	32.5
Electronically controlled microwave power	•
Microwave power levels in W	
Maximum microwave power in W	900
Grill power rating in W	800
Appliance width in mm	520
Appliance height in mm	305
Appliance depth in mm	422
Weight in kg	16.5
Total rated load in kW	2.3
Voltage in V	220-240
Frequency in Hz	50
Fuse rating in A	13
Number of phases	1
Mains cable with plug	•
Length of supply lead in m	1.20

M 6012 SC

Freestanding microwave oven
with knob controls on the side at an attractive entry-level price.



EAN: 4002515275252 / Material number: 09546480 / Old Material Number: 24601250GB


Replacing lamps

Service

Accessories included	
Grilling rack	1
Gourmet plate	1
Food cover	1
Turntable	1

M 6012 SC

Freestanding microwave oven
with knob controls on the side at an attractive entry-level price.



M8201, M8201-1, M6012SC (installation drawing)