

PG 8055 [MK SPEED]

Freestanding fresh water dishwasher
with baskets for restaurants, schools and bakeries.



- Max. cleaning performance*: 225 plates/h
- Versatile processing of two wire or plastic baskets per cycle
- Simple to operate thanks to clear fascia panel design
- Always the right programme – item-specific solutions
- First-class results thanks to freshwater wash system

* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002515453568 / Material number: 09849650 / Old Material Number: 61805501IRL

Construction type and design	
Construction type	Freestanding dishwasher, front loader
Range	Professional
Model	Speed
Wash system	Fresh water front loader
Number of levels	2
Front	Lotus white
Lid	Lotus White
Side panels	Lotus White
Application	
Suitable for small restaurants/bars	•
Suitable for hospitality industry	•
Suitable for guesthouses	•
Suitable for canteens	•
Suitable for sports clubs	•
Performance data	
Circulation pump Qmax in l/min.	390
Shortest programme duration in min.	8
Maximum final rinse temperature in °C	70
Cleaning performance, plates/h	225
Cleaning performance, baskets/h	15
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	15000
Controls	
Control system	TouchControl
Programme selection	Touch on MSetal
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	8.50
Total connected load in kW	8.90
Fuse rating in A	16
Length of mains connection cable in m	1.70
Possible voltage variant 1	
Electrical connection	AC 230V 50HZ
Heater rating in kW	3.00
Total connected load in kW	3.40
Fuse rating in A	16
Water connection/drainage	
Cold or hot water [number]	1
Required flow pressure in bar	0.40-10.00
Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•
Maximum water hardness in mmol/l	10.70

PG 8055 [MK SPEED]

Freestanding fresh water dishwasher
with baskets for restaurants, schools and bakeries.



EAN: 4002515453568 / Material number: 09849650 / Old Material Number: 61805501IRL

Water protection system	Waterproof system
Water consumption per wash cycle in l	17.50
Dimensions and weight	
External dimensions, height in mm	820
External dimensions with lid, height in mm	835
External dimensions, net width in mm	600
External dimensions, net depth in mm	600
External dimensions, gross height in mm	940
External dimensions, gross width in mm	675
External dimensions, gross depth in mm	745
Usable space in wash cabinet, height in mm	559
Usable space in wash cabinet, width in mm	530
Usable space in wash cabinet, depth of upper baske	474
Usable space in wash cabinet, depth of lower basket in mm	505
In-feed height above floor in mm	216
Net weight [kg]	63
Gross weight in kg	69
Maximum floor loading in N	1200
Emissions data	
Emissions – sound pressure at workplace	47 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	59.0
Heat dissipation into the room in MJ/h	1.08
Programmes	
Universal	•
Short	•
Hygiene	•
Cold/Pre-wash	•
Glasses	•
Beer glasses	•
Plastics	•
Energy save/Eco	•
Intensive	•
Reactivation	•
Drainage	•
Basket design	
1 x O 891 upper basket for cups	•
1 x U 890 lower basket for inserts	•
1 x E 810 insert for dessert plates	•
2 x E 165 inserts for cutlery	•
2 x E 216 inserts for plates	•
Height-adjustable upper basket	•
Features	
Drying	without
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made from high-quality stai	•
In-door salt container	•
Perfect GlassCare	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Adjustable wash temperature	•

PG 8055 [MK SPEED]

Freestanding fresh water dishwasher
with baskets for restaurants, schools and bakeries.



EAN: 4002515453568 / Material number: 09849650 / Old Material Number: 61805501IRL

Adjustable rinse time	•
Optical interface	•
A wide range of accessories (optional)	•
Connection options	
External dispensing module for cleaning agent or rinsing agent	•
Standards, certs, symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
EMC	•
Interference suppression	•
VDE	•
DIN 10512	•
EN 1717	•