

H 6267 B

Oven

with Moisture Plus and automatic programmes for perfect cooking results.



- 7-segment display with rotary selector – EasyControl
- Perfect baking and roasting results – Moisture plus
- Particularly easy to clean – PerfectClean finish
- Easy to use on all levels – FlexiClip runners
- Fewer fingerprints and easy to clean – CleanSteel



EAN: 4002515557945 / Material number: 09974120 /
Old Material Number: 22626752GB

General information	
Model identifier	H 6267 B
Manufacturer material number	09974120
EAN number	4002515557945
Construction type and design	
Built-in oven	•
Colour	Stainless steel/Clean Steel
PureLine	•
Retractable rotary controls	•
Convenience features	
Rapid heat-up	•
Operating modes	
Defrosting	•
Auto roast	•
Fan plus	•
Intensive bake	•
Moisture plus	•
Conventional heat	•
Bottom heat	•
Fan grill	•
Grill	•
User convenience	
Display	EasyControl
Time of day display	•
Minute minder	•
Programmable cooking duration	•
Actual temperature display	•
Recommended temperature	•
Individual settings	•
Buzzer when desired temperature is reached	•
Efficiency	
Energy efficiency class (A+++ – D)	A+
Cleaning and care	
Stainless steel/CleanSteel finish	•
Oven compartment with PerfectClean and catalytically enamelled liners	•
Hinged grill element	•
CleanGlass door	•
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Technical data	
Oven compartment volume in l	76
No. of shelf levels	5
Numbered shelf levels	•
Mains plug	3 pole without plug
Niche width min. in mm	560

H 6267 B

Oven

with Moisture Plus and automatic programmes for perfect cooking results.



EAN: 4002515557945 / Material number: 09974120 /
Old Material Number: 22626752GB

Niche width max. in mm	568
Niche height min. in mm	593
Niche height max. in mm	595
Niche depth in mm	550
Weight in kg	42.0
Total rated load in kW	3.50
Voltage in V	230
Frequency in Hz	50
Fuse rating in A	16
Number of phases	1
Mains cable	•
Length of mains connection cable in m	1.70