

## PG 8591 [WW AD]

Thermal disinfector

with hot and AD water connection, liquid dispensing & DryPlus hot air drying.



- Perf./cycle, e.g. 44 transmission instruments or 44 suction devices
- Safety through monitoring – wash pressure and spray arm monitoring
- Efficient hot air drying – DryPlus
- Total security – link to process documentation possible

EAN: 4002515558393 / Material number: 10087460 / Old Material Number: 63859121GB

<b>Construction type and version</b>	
Construction type	Freestanding, can be built-under, slimline
Casing	White
Can be built-under	•
AutoClose – automatic door lock	•
Buzzer, acoustic signal at end of programme	•
Service-friendly design	•
<b>Application</b>	
Suitable for dental surgeries	•
<b>Capacity</b>	
Suction devices per cycle [number]	44
Transmission instruments per cycle [number]	44
<b>Performance data</b>	
Circulation pump, Qmax in l/min	500
Wash cabinet usable capacity in l	145.00
Tested operating hours	15000
Maximum final rinse temperature in °C	93
<b>Control system</b>	
Control type	TouchControl
Programme selection	Touch on MSetal
Direct-access pushbuttons	•
Max. delay start in h	24
Programmability	programmable
Programmes [number]	7
Free programme positions [number]	2
A0 value controls	•
Automatic programme restart	•
Time left display	•
Programme sequence display	•
Selectable display languages	•
<b>Standard electrical connection</b>	
Electrical connection	AC 230V 50HZ
Electric heater rating in kW	5.50
Total rated load in kW	6.30
Fuse rating in A	30-32
Length of mains connection cable in m	1.90
<b>Possible voltage variant 1</b>	
Electrical connection	3N AC 400V 50HZ
Electric heater rating in kW	8.50
Total rated load in kW	9.30
Fuse rating in A	15-16
<b>Possible voltage variant 2</b>	
Electrical connection	AC 230V 50HZ
Electric heater rating in kW	2.50
Total rated load in kW	3.30
Fuse rating in A	15-16
<b>Water connection/drainage</b>	
Cold water [number]	1
Cold water for steam condenser [number]	1

PG 8591 [WW AD]

Thermal disinfecter

with hot and AD water connection, liquid dispensing & DryPlus hot air drying.



EAN: 4002515558393 / Material number: 10087460 / Old Material Number: 63859121GB

Hot water [number]	1
Required flow pressure in kPa	200-1000
DI water [number]	1
Maximum delivery head for drain pump in cm	100
Maximum water hardness (cold water/hot water) in mmol/l	10.70
Drain pump [DN]	22
Integrated water softener	•
Water protection system	Waterproof system
<b>Dimensions and weight</b>	
Net weight in kg	78
<b>Drying unit</b>	
Integrated drying unit	•
Fan in kW	0.30
Heater element in kW	2.20
Air throughput in m <sup>3</sup> /h	60
Time setting in 1-minute increments	0-120
HEPA filter class	H13
HEPA filter filtration efficiency (in accordance with DIN EN 1822) in %	99.95
<b>Dimensions and weight</b>	
External dimensions, net height in mm	835
External dimensions, net width in mm	600
External dimensions, net depth in mm	600
External dimensions, gross height in mm	940
External dimensions, gross width in mm	675
External dimensions, gross depth in mm	745
Wash cabinet, usable height in mm	520
Wash cabinet, usable width in mm	530
Wash cabinet, depth of upper basket in mm	474
Wash cabinet, depth of lower basket in mm	520
Gross weight in kg	85
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.65
<b>Features</b>	
Volume flow control	•
Interface for process documentation (optional)	•
Customer Service interface	•
Extensive components (option)	•
<b>Programmes</b>	
Vario TD Intensive	•
Vario TD Dental	•
Vario TD Dental +	•
Special 93 °C-10'	•
<b>Features</b>	
1 door dispenser for rinsing agent	•
1 dispenser pump for liquid cleaning agent	•
Steam condenser	•
Spray pressure monitoring	•
Spray arm monitoring	•
Multi-component filter system	•

PG 8591 [WW AD]

Thermal disinfector

with hot and AD water connection, liquid dispensing & DryPlus hot air drying.



EAN: 4002515558393 / Material number: 10087460 / Old Material Number: 63859121GB

Variable-speed heater pump	•
Load carrier – direct coupling	•
DryPlus	•
In-door salt container	•
Wash cabinet seamlessly welded using laser technology	•
Heater elements outside wash cabinet	•
Wash cabinet made from high-quality stainless steel (1.4301/304)	•
<b>Connection options</b>	
RS 232 serial interface (optional)	•
WiFi via DataDiary (optional)	•
Ethernet interface (optional)	•
External dispensing modules	•
<b>Standards, test certificates and symbols</b>	
VDE (electrical safety)	•
IP safety class according to EN 60529: IP 21	•
EN 61010-2-040	•
RoHS guideline 2011/65/EU	•
WRAS	•
EU medical device class IIb	•
<b>Standards, test certificates and symbols</b>	
EN 61010-1	•