

## B 3826 FashionMaster

### Steam ironing system

with display and 2-level ironing board fan for perfect ironing results.



- Uniform steam distribution – Miele honeycomb soleplate
- Professional ironing results due to 4.0 bar steam pressure
- Convenient set-up/storage – 1-2 lift system
- Perfect ironing with support of the active ironing board
- Easy ironing with the fan set to Fan power level

EAN: 4002515781210 / Material number: 10546440 /  
Old Material Number: 13382621GB

#### General information

|                              |                      |
|------------------------------|----------------------|
| Model identifier             | B 3826 FashionMaster |
| Manufacturer material number | 10546440             |
| EAN number                   | 4002515781210        |

#### Design

|                            |                        |
|----------------------------|------------------------|
| Iron colour                | Anthracite/lotus white |
| Ironing board cover colour | Anthracite             |
| Display                    | 1-line text display    |

#### Perfect ironing results

|                                                       |     |
|-------------------------------------------------------|-----|
| Honeycomb soleplate                                   | •   |
| Steam pressure in bar                                 | 4.0 |
| Steam quantity in g/min                               | 100 |
| Vertical steam                                        | •   |
| Steam starting from temperature level                 | 2   |
| Steam burst                                           | •   |
| Continuous steam                                      | •   |
| Active ironing table (inflation and suction function) | •   |
| Suction function                                      | •   |
| 2-stage fan                                           | •   |
| Non-stick soleplate                                   | •   |
| Proven virus hygiene                                  | •   |

#### Time-saving ironing

|                                        |      |
|----------------------------------------|------|
| Water container volume in l            | 1.25 |
| Removable water container              | •    |
| Permanently refillable water container | •    |
| Multi-layer ironing                    | •    |

#### User convenience

|                                                          |            |
|----------------------------------------------------------|------------|
| All-in-one                                               | •          |
| 1-2 Lift system                                          | •          |
| Variable height adjustment with gas pressure stay, in mm | 830 - 1020 |
| Castors gentle on the floor                              | •          |
| Ironing board with Comfort Zone                          | •          |
| Fan safety switch-on/switch-off                          | •          |
| Fan memory function                                      | •          |
| Choice of language                                       | •          |
| Guided first-time use                                    | •          |
| Guided descaling                                         | •          |
| Automatic descaling                                      | •          |
| Automatic rinsing                                        | •          |
| Storage compartment for iron                             | •          |
| Storage compartment for mains cable and accessories      | •          |

#### Safety

|                   |   |
|-------------------|---|
| CoolDown function | • |
| AutoOff function  | • |

#### Technical data

|                           |      |
|---------------------------|------|
| Dimensions in mm (width)  | 470  |
| Dimensions in mm (height) | 970  |
| Dimensions in mm (depth)  | 1480 |

## B 3826 FashionMaster

Steam ironing system

with display and 2-level ironing board fan for perfect ironing results.



EAN: 4002515781210 / Material number: 10546440 /

Old Material Number: 13382621GB

|                                   |            |
|-----------------------------------|------------|
| Dimensions in mm (width), folded  | 470        |
| Dimensions in mm (height), folded | 1280       |
| Dimensions in mm (depth), folded  | 370        |
| Ironing surface area in mm        | 1200 x 400 |
| Frequency in Hz                   | 50 - 60    |

### Accessories included

|                                            |   |
|--------------------------------------------|---|
| Non-stick soleplate                        | • |
| Steam hose holder                          | • |
| Test strips for determining water hardness | • |
| Descaling tablets                          | • |

### Available display languages

Available display languages via MultiLingua

? ? ? ? ? ? ? , ?  
 ? , ? ? ? ? ? , deutsch,  
 dansk, english (AU),  
 english (GB), english (US),  
 suomi, français, ελληνικά,  
 italiano, ? ? ? , ? ? ? ,  
 hrvatski, bahasa malaysia,  
 nederlands, norsk, polski,  
 português, română,  
 русский, svenska, srpski,  
 slovenčina, slovenščina,  
 español, čeština, türkçe,  
 українська, magyar