

PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



- Powerful – 650 m³/h on the booster setting
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – for extraction or recirculation

A

EAN: 4002515792971 / Material number: 10565920 / Old Material Number: 28416854GB

| Construction type | |
|---|--------------------|
| Wall mounted cooker hood | • |
| Operating modes | |
| Type of air guide | Can be retrofitted |
| Recirculation conversion kit (order separately) | DUW 20 |
| Active charcoal filter (order separately) | DKF 12-P |
| Design | |
| Colour | Stainless steel |
| RAL colours available as customisation on request | • |
| Customisation possible on request | • |
| User convenience | |
| Electronic controls | • |
| Power levels (number without Booster level) | 3 |
| Programmable Booster level switch-off | • |
| Easy-to-clean canopy interior – CleanCover | • |
| Efficiency and sustainability | |
| Energy efficiency class (A+++ – D) | A |
| Annual energy consumption in kWh/year | 47.0 |
| Fluid dynamic efficiency class | A |
| Lighting efficiency class | A |
| Grease filtering efficiency class | A |
| Filter system | |
| Number of dishwasher-safe stainless steel grease filters (10-ply) | 2 |
| Lighting | |
| LED | • |
| Number x W | 2 x 3 W |
| Light intensity in lx | 330 lx |
| Colour temperature in K | 3000 Kelvin |
| Fan | |
| Dual-action fan | • |
| AC motor | • |
| Exhaust air | |
| Air throughput in Level 1 (m ³ /h) according to EN 61591 | 265 |
| Air throughput in Level 2 (m ³ /h) according to EN 61591 | 320 |
| Air throughput in Level 3 (m ³ /h) according to EN 61591 | 395 |
| Air throughput in Booster level (m ³ /h) according to EN 61591 | 650 |
| Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3 | 47.0 |
| Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3 | 52.0 |
| Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3 | 56.0 |
| Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3 | 67.0 |
| Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13 | 32.0 |
| Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13 | 37.0 |
| Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13 | 41.0 |

PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



EAN: 4002515792971 / Material number: 10565920 / Old Material Number: 28416854GB

Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13 52.0

Recirculation

Air throughput in Level 1 (m³/h) according to EN 61591 190

Air throughput in Level 2 (m³/h) according to EN 61591 270

Air throughput in Level 3 (m³/h) according to EN 61591 330

Air throughput in Booster level 1 (m³/h) according to EN 61591 460

Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3 54.0

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3 60.0

Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3 64.0

Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3 71.0

Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13 39.0

Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13 45.0

Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13 48.0

Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13 56.0

Safety

Safety switch-off

•

Technical data

Overall hood height for extraction mode and external in mm 685–1005

Overall hood height for recirculation and external in mm 815–1135

Overall height for vented and external in in. (mm) 685

Canopy width in mm 598

Overall height for extraction mode and external mode cooker hoods in mm 1005

Canopy height in mm 62

Overall height for recirculation in in. (mm) 815

Canopy depth in mm 500

Overall height for recirculation mode cooker hoods in mm 1135

Minimum height above electric hobs in mm 450

Net weight in kg 21.0

Length of supply lead in m 1.5

Standard plug fitted

•

Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm 650

Total rated load in kW 0.22

Voltage in V 230

Fuse rating in A 10

Number of phases 1

Frequency in Hz 50

Installation notes

Extraction ducting connection at top

•

Extraction connection at top and rear

•

Diameter of exhaust duct in mm 150

Telescopic chimney

•

PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting




EAN: 4002515792971 / Material number: 10565920 / Old Material Number: 28416854GB

| Accessories included | |
|--|----------|
| Non-return flap | • |
| Optional accessories | |
| Active charcoal filter | Nein |
| Active charcoal filter, can be reactivated | DKF 12-R |

PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



PUR68W, PUR62W Living, DA416-6, DA416-7 (Installation drawing)

1) Extraction, 2) Recirculation, 3) Ventilation grille at top for recirculation, 4+5) Installation cut-out (5 not required for recirculation)