

## PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



- Powerful – 650 m<sup>3</sup>/h on the booster setting
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – for extraction or recirculation



EAN: 4002515792971 / Material number: 10565920 / Old Material Number: 28416854GB

<b>Construction type</b>	
Wall mounted cooker hood	•
<b>Construction type and design</b>	
Colour	Stainless steel
<b>Operating modes</b>	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUW 20
Active charcoal filter (order separately)	DKF 12-P
<b>Design</b>	
RAL colours available as customisation on request	•
<b>User convenience</b>	
Electronic controls	•
Power levels (number without Booster level)	3
Booster levels	1
Programmable Booster level switch-off	•
Easy-to-clean canopy interior – CleanCover	•
<b>Efficiency and sustainability</b>	
Energy efficiency class (A+++ – D)	A
Annual energy consumption in kWh/year	47.0
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
<b>Lighting</b>	
LED	•
Number x W	2 x 3 W
Light intensity in Lx	330 lx
Colour temperature in K	3000 Kelvin
<b>Fan</b>	
Dual-action fan	•
AC motor	•
<b>Exhaust air</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	265
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	320
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	395
Air throughput in Booster level (m <sup>3</sup> /h) according to EN 61591	650
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	47.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	52.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	56.0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	67.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	37.0

## PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



EAN: 4002515792971 / Material number: 10565920 / Old Material Number: 28416854GB

Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	41.0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	52.0
<b>Recirculation</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	190
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	270
Air throughput in Intensive level (m <sup>3</sup> /h) according to EN 61591	460
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	330
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	54.0
Noise power level in Intensive level (dB(A) re 1 pW) according to EN 60704-3	71.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	60.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	64.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	39.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	45.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	48.0
Noise pressure level in Intensive level (dB(A) re 20 µPa) according to EN 60704-2-13	56.0
<b>Safety</b>	
Safety switch-off	•
<b>Technical data</b>	
Overall hood height for extraction mode and external in mm	685–1005
Overall hood height for recirculation and external in mm	815–1135
Overall height for vented and external in in. (mm)	685
Canopy width in mm	598
Overall height for extraction mode and external mode cooker hoods in mm	1005
Canopy height in mm	62
Overall height for recirculation in in. (mm)	815
Canopy depth in mm	500
Overall height for recirculation mode cooker hoods in mm	1135
Minimum height above electric hobs in mm	450
Net weight in kg	21.0
Length of supply lead in m	1.5
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0.22
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
<b>Installation notes</b>	
Extraction ducting connection at top	•
Extraction connection at top and rear	•

PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting




EAN: 4002515792971 / Material number: 10565920 / Old Material Number: 28416854GB

Diameter of exhaust duct in mm	150
Telescopic chimney	•
<b>Accessories included</b>	
Non-return flap	•
<b>Optional accessories</b>	
Active charcoal filter	Nein
Active charcoal filter, can be reactivated	DKF 12-R

## PUR 68 W

Wall mounted cooker hood

with EasySwitch light-touch switches for convenient operation and LED lighting



PUR68W, PUR62W Living, DA416-6, DA416-7 (Installation drawing)

1) Extraction, 2) Recirculation, 3) Ventilation grille at top for recirculation, 4+5) Installation cut-out (5 not required for recirculation)