

DAR 1155

Extractor unit

for perfectly combining with Range Cookers or Range Tops.



- Customised kitchen design – fully integrated in 1155 mm
- Powerful fan – up to 650 m³/h
- Perfect illumination – LED ClearView lighting
- Dishwasher-proof – 4 high-quality stainless steel grease filters
- Safe and easy to clean – Miele CleanCover

B

EAN: 4002515815755 / Material number: 10598380 / Old Material Number: 28115550GB

Construction type	
Integrated extractor	•
Operating modes	
Type of air guide	Exhaust air
User convenience	
Rotary knob	•
Electronic controls	•
Power levels (number without Booster level)	3
Temperature sensor	•
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	B
Annual energy consumption in kWh/year	69.5
Fluid dynamic efficiency class	B
Lighting efficiency class	A
Grease filtering efficiency class	C
Cleaning and care	
Dishwasher-safe grease collection channel	•
Filter system	
Number of dishwasher-safe stainless steel filters	4
Lighting	
LED	•
Number x W	4 x 3 W
Fan	
Dual-action fan	•
AC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	200
Air throughput in Level 2 (m ³ /h) according to EN 61591	300
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in Booster level (m ³ /h) according to EN 61591	650
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	39.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	48.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	54.0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	67.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	25.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	34.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	40.0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	53.0
Safety	
Safety switch-off	•
Technical data	
Canopy width in mm	1155

DAR 1155

Extractor unit

for perfectly combining with Range Cookers or Range Tops.




EAN: 4002515815755 / Material number: 10598380 / Old Material Number: 28115550GB

Canopy height in mm	449
Canopy depth in mm	579
Minimum height above electric hobs in mm	450
Net weight in kg	28.0
Length of supply lead in m	1.5
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0.21
Voltage in V	230
Fuse rating in A	15
Number of phases	1
Installation notes	
Extraction ducting connection at top	•
Extraction ducting connection at rear	•
Extraction ducting connection on side	•
Extraction ducting connection at top, rear, and side	•
Diameter of exhaust duct in mm	150
Accessories included	
Non-return flap	•

DAR 1155

Extractor unit

for perfectly combining with Range Cookers or Range Tops.



DAR1155 (installation drawing)