

PG 8130

Free-standing dishwasher

For crockery mountains in office kitchens, tea rooms and utility areas.



- Wash performance: 13 place settings in just 19 min.*
- Requires an electrical connection for AC 230V 50HZ
- Intuitive to operate thanks to clear control panel design
- Everything completely dry – AutoOpen assisted drying
- The best care for your glasses – Perfect GlassCare
- Easy communication – WiFi Connect

* Depending on site conditions (temperature of incoming water / power connection) values given may vary.



EAN: 4002515818794 / Material number: 10638500 / Old Material Number: 61813006GB

Construction type and version

Construction type	Freestanding dishwasher, front loader
Range	ProfiLine
Wash system	Fresh water front loader
Number of levels	2
Front	Brilliant white
Lid	Plastic
Side panels	Brilliant White

Application

Suitable for guesthouses	•
Suitable for universities and schools	•
Suitable for offices	•
Suitable for domestic use	•
Suitable for small businesses	•
Suitable for sports clubs	•

Performance data

Circulation pump Qmax in l/min.	190
Shortest programme duration in min.	19
Maximum final rinse temperature in °C	82
Cleaning performance, place settings/cycle	13

Control system

Control system	Electronic controls
Programme selection	Programme selector buttons
Max. delay start in h	24
Time left display	•
Choice of display language	•

Standard electrical connection

Electrical connection	AC 230V 50HZ
Heater rating in kW	6.50
Total connected load in kW	6.70
Fuse rating in A	32
CEE plug	•
Length of mains connection cable in m	1.70

Possible voltage variant 1

Electrical connection	AC 230V 50HZ
Heater rating in kW	2.10
Total connected load in kW	2.30
Fuse rating in A	13

Water connection/drainage

Cold or hot water [number]	1
Required flow pressure in bar	0.30-10.00
Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•
Maximum water hardness in mmol/l	6.50
Water protection system	Waterproof system

Dimensions and weight

External dimensions, height in mm	845
-----------------------------------	-----

PG 8130

Free-standing dishwasher

For crockery mountains in office kitchens, tea rooms and utility areas.



EAN: 4002515818794 / Material number: 10638500 / Old Material Number: 61813006GB

External dimensions with lid, height in mm	845
External dimensions, net width in mm	598
External dimensions, net depth in mm	600
External dimensions, gross height in mm	970
External dimensions, gross width in mm	670
External dimensions, gross depth in mm	690
Usable space in wash cabinet, height in mm	540
Usable space in wash cabinet, width in mm	510
Usable space in wash cabinet, depth of upper basket	450
Usable space in wash cabinet, depth of lower basket in mm	450
In-feed height above floor in mm	210
Net weight [kg]	62
Gross weight in kg	70
Maximum floor load in N/m ²	1000
Emissions data	
Emissions – sound pressure at workplace	38 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	45.0
Heat dissipation into the room in MJ/h	2.52
Programmes	
Universal	•
Short	•
Hygiene	•
Cold/Pre-wash	•
Glasses	•
Plastics	•
Energy save/Eco	•
Intensive	•
Basket design	
MaxiComfort baskets	•
Cutlery basket	•
Features	
Drying	Extra drying, Recirculation condensation drying, AutoOpen assisted drying
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made from high-quality stainless steel	•
ComfortClose	•
Perfect GlassCare	•
Safety lock	•
Adjustable final rinse temperature	•
Optical interface	•
SmartStart	•
FlexiTimer with EcoStart	•
MobileControl	•
ShopConn@ct	•
WiFi module	•
Efficiency and sustainability	
Load size of the ECO programme in place settings	13
Energy efficiency class (A–G)	E
Energy consumption of the ECO program per 100 cycles	93

PG 8130

Free-standing dishwasher

For crockery mountains in office kitchens, tea rooms and utility areas.



EAN: 4002515818794 / Material number: 10638500 / Old Material Number: 61813006GB

Water consumption of the ECO programme per cycle in l	13.8
Acoustic airborne noise emission class (A–D)	C
Acoustic airborne noise emission in dB(A) re 1 pW	46
Programme running time of the ECO programme in min	217
Connection options	
External dispensing module for liquid detergent	•
Standards, test certificates and symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
Interference suppression	•
VDE	•
DIN EN 17735	•
EN 1717	•