

Classic C1 Junior PowerLine – SBAF3

Cylinder vacuum cleaner

High suction power for thorough vacuuming at an attractive entry level price.



- High suction power – 800 W
- Versatile applications – universal floorhead
- Particularly lightweight – 5.8 kg with vacuuming accessories
- Effortless vacuuming of large areas with a 9 m operating radius

EAN: 4002515826850 / Material number: 10660630 /
Old Material Number: 41BAF332GB

General information	
Model identifier	Classic C1 Junior PowerLine – SBAF3
Manufacturer material number	10660630
EAN number	4002515826850
Construction type	
Cylinder vacuum cleaner with dustbag	•
Product brand	Classic C1
Motor type	PowerLine
Product type	SBAF3
Construction type and design	
Colour	Tech blue
User convenience	
Electronic suction power control	6-stage rotary selector
Ergonomic carrying handle	•
Ergonomic handle	•
Silence system	•
Suction tube	EasyLock sectioned suction tube
Park system for pauses during vacuuming	•
Park system for storing	on one side
Mobility	
Castors with steel shaft, gentle on floors	•
3-point manoeuvrability	•
Operating radius in m	9
Cable length in m	5.5
Filter system	
Vacuum cleaner bag type	HyClean GN
Dustbag volume in l	4.5
Dustbag change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic dustbag positioning	•
Technical data	
Power	800
Width in mm	463
Height in mm	221
Depth in mm	279
Weight in kg	5.7
Accessories included	
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush	•
Floorhead SBD 355-3	•