


## PG 8130 i

### Integrated dishwasher

For crockery mountains in office kitchens, tea rooms and utility areas.



- Wash performance: 13 place settings in just 17 min.\*
- Requires an electrical connection for AC 230V 50HZ
- Intuitive to operate thanks to clear control panel design
- Everything completely dry – AutoOpen assisted drying
- The best care for your glasses – Perfect GlassCare
- Easy communication – WiFi Conn@ct

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.




EAN: 4002515960738 / Material number: 10815260 / Old Material Number: 61813047GB

Construction type and version	
Construction type	Semi-integrated dishwasher
Range	ProfiLine
Wash system	Fresh water front loader
Number of levels	2
Front	Without front
Side panels	Galvanised
Application	
Suitable for guesthouses	•
Suitable for universities and schools	•
Suitable for offices	•
Suitable for domestic use	•
Suitable for small businesses	•
Suitable for sports clubs	•
Performance data	
Circulation pump Qmax in l/min.	190
Shortest programme duration in min.	17
Maximum final rinse temperature in °C	82
Cleaning performance, place settings/cycle	13
Control system	
Control system	Electronic controls
Programme selection	Programme selector buttons
Max. delay start in h	24
Time left display	•
Choice of display language	•
Standard electrical connection	
Electrical connection	AC 230V 50HZ
Heater rating in kW	6.50
Total connected load in kW	6.70
Fuse rating in A	32
CEE plug	•
Length of mains connection cable in m	1.70
Possible voltage variant 1	
Electrical connection	AC 230V 50HZ
Heater rating in kW	2.10
Total connected load in kW	2.30
Fuse rating in A	13
Water connection/drainage	
Cold or hot water [number]	1
Required flow pressure in bar	0.30-10.00
Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•
Maximum water hardness in mmol/l	6.50
Water protection system	Waterproof system
Dimensions and weight	
External dimensions, height in mm	805
External dimensions, net width in mm	598
External dimensions, net depth in mm	570

## PG 8130 i

### Integrated dishwasher

For crockery mountains in office kitchens, tea rooms and utility areas.



EAN: 4002515960738 / Material number: 10815260 / Old Material Number: 61813047GB

External dimensions, gross height in mm	970
External dimensions, gross width in mm	670
External dimensions, gross depth in mm	690
Usable space in wash cabinet, height in mm	540
Usable space in wash cabinet, width in mm	510
Usable space in wash cabinet, depth of upper basket	450
Usable space in wash cabinet, depth of lower basket in mm	450
In-feed height above floor in mm	210
Net weight [kg]	55
Gross weight in kg	64
Maximum floor loading in N	1000
<b>Emissions data</b>	
Emissions – sound pressure at workplace	38 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	45.0
Heat dissipation into the room in MJ/h	2.52
<b>Programmes</b>	
Universal	•
Short	•
Hygiene	•
Cold/Pre-wash	•
Glasses	•
Plastics	•
Energy save/Eco	•
Intensive	•
<b>Basket design</b>	
MaxiComfort baskets	•
Cutlery basket	•
<b>Features</b>	
Drying	Extra drying, AutoOpen assisted drying, Recirculation condensation drying
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made from high-quality stainless steel	•
ComfortClose	•
Perfect GlassCare	•
Safety lock	•
Adjustable final rinse temperature	•
Optical interface	•
SmartStart	•
FlexiTimer with EcoStart	•
MobileControl	•
ShopConn@ct	•
WiFi module	•
<b>Efficiency and sustainability</b>	
Load capacity of the ECO program in place settings	13
Energy efficiency class (A–G)	E
Energy consumption of the ECO program per 100 cycles	93
Water consumption of the ECO program per cycle in l	13.8
Noise emission rating (A–D)	C
Noise emission in dB(A) re 1 pW	46

**Miele**

PG 8130 i

Integrated dishwasher

For crockery mountains in office kitchens, tea rooms and utility areas.