

K 37672 iD

Built-in refrigerator

With PerfectFresh Pro and FlexiLight for longer freshness and optimum lighting.



- Food stays fresh for up to 5 x longer with PerfectFresh Pro
- Individually adjustable glass shelf lighting thanks to FlexiLight
- Door shelves can be cleaned in the dishwasher – ComfortClean



EAN: 4002515976647 / Material number: 10845350 / Old Material Number: 36376720GB

<b>Appliance category</b>	
Refrigerator	•
<b>Construction type</b>	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Refrigeration section lighting	FlexiLight
PerfectFresh Pro LED lighting	•
<b>User convenience</b>	
Networking with Miele@home	•
Accessories required	XKS 3130 W
Freshness system	PerfectFresh Pro
ComfortClean	•
DynaCool	•
SoftClose	•
SelfClose	•
<b>Controls</b>	
Operating concept	TouchControl
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
Automatic SuperCool	•
No. of temperature zones	2
Sabbath mode	•
<b>Fridge/Fridge section</b>	
No. of shelves	6
of which illuminated	4
Chrome-plated metal bottle rack	•
No. of crisper drawers	3
Number of inner door racks for tinned food	3
Door rack for bottles	2
Door shelves	5
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	E
Annual energy consumption in kWh	155.86
Energy consumption in 24 h in kWh	0.42
<b>Safety</b>	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•
<b>Technical data</b>	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1770

K 37672 iD

Built-in refrigerator

With PerfectFresh Pro and FlexiLight for longer freshness and optimum lighting.



EAN: 4002515976647 / Material number: 10845350 / Old Material Number: 36376720GB

Appliance depth in mm	544
Weight in kg	70.8
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	26
Climate class	SN-T
Refrigerator compartment in l	308
including PerfectFresh zone in l	94
4* freezer compartment in l	0
Total usable capacity in l	308
Storage time in case of fault in h	0
Acoustic airborne noise emission class (A–D)	C
Sound emissions in dB(A) re 1 pW	37
Current consumption (mA)	1200
Voltage in V	220-240
Fuse rating in A	13
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.1
Replacing lamps	Customer Service
<b>Accessories supplied</b>	
Butter dish	•
Egg tray	•

