

SC

Steam condenser

For effective moisture removal from and cooling of exhaust air.



- Only suitable for use in combination with a drying unit
- Can be connected to on-site cooling water circuit

EAN: 4002516024323 / Material number: 10928990 / Old Material Number: 69251300D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8615	•
PLW 8616	•
PLW 8617	•
Product properties	
Material	Stainless steel
Dimensions and weight	
External dimensions, gross height in mm	770
External dimensions, gross width in mm	1200
External dimensions, gross depth in mm	800
Net weight in kg	14.00
Gross weight in kg	135.00
Standards, test certificates and symbols	
UL	•