

DP [50Hz]

Drain pump

For converting machines with drain valves to drain pumps.



- For installations without a floor drain

EAN: 4002516024057 / Material number: 10931330 / Old Material Number: 69240003D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PLW 8615	•
PLW 8616	•
PLW 8617	•
<b>Product properties</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black, White, Grey
<b>Area of application</b>	
Reprocessing of laboratory glassware	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	0
External dimensions, net width in mm	0
External dimensions, net depth in mm	0
External dimensions, gross height in mm	180
External dimensions, gross width in mm	390
External dimensions, gross depth in mm	390
Net weight in kg	3.88
Gross weight in kg	5.73