

KM 3034-1

Gas hob

with electronic functions for maximum safety and user convenience.



- Optimal – single-handed operation via rotary dials and QuickStart
- Elegant design – 806 mm wide gas on glass hob
- Particularly versatile – 5 burners incl. 1 dual wok
- Extremely safe – GasStop&Restart function
- Easy cleaning – dishwasher-safe ComfortClean pot rests

EAN: 4002516120216 / Material number: 10939800 / Old Material Number: 26303451GB

| Heating type | |
|---|-------------------|
| Heating type | Gas |
| Construction type | |
| Independent of cooker | • |
| Design | |
| Elegant glass ceramic surface | • |
| Ceramic surface colour | Black |
| Cast iron pot rests (matt black enamelled) | • |
| Cooking zone details | |
| Number of cooking zones | 5 |
| Gas burner power rating | |
| Small burner in kW | 1.00 |
| Medium burner in kW | 1.70 |
| Large burner in kW | 2.70 |
| Dual wok burner in kW | 4.70 |
| 1st cooking zone/cooking area | |
| Position | front left |
| Type | High-speed burner |
| 2nd cooking zone/cooking area | |
| Position | rear left |
| Type | Economy burner |
| 3rd cooking zone/cooking area | |
| Position | Centred |
| Type | Dual wok burner |
| 4th cooking zone/cooking area | |
| Position | rear right |
| Type | Standard burner |
| 5th cooking zone/cooking area | |
| Position | front right |
| Type | Standard burner |
| User convenience | |
| Display colour | Red |
| Operation via knobs | • |
| Electronic ignition with single-hand operation | • |
| QuickStart | • |
| Cleaning and care | |
| Easy to clean ceramic glass | • |
| Dishwasher-proof pot rests | • |
| Safety | |
| Heat indicator | • |
| Operational indicator | • |
| GasStop & ReStart | • |
| Technical data | |
| Dimensions (H x W x D) in mm | 53 x 806 x 526 |
| Dimensions in mm (width) | 806 |
| Dimensions in mm (height) | 53 |
| Dimensions in mm (depth) | 526 |
| Cutout dimensions in mm (width) with surface-mounted installation | 780 |

KM 3034-1

Gas hob

with electronic functions for maximum safety and user convenience.




EAN: 4002516120216 / Material number: 10939800 / Old Material Number: 26303451GB

| | |
|---|---------------|
| Cutout dimensions in mm (depth) with surface-mounted installation | 500 |
| Casing height incl. connection box in mm | 78 |
| Weight in kg | 20 |
| Total rated load in kW | 0.00-0.00 |
| Length of supply lead in m | 1.4 |
| Dimensions in mm (width) | Hinten rechts |
| Voltage in V | 220-240 |
| Frequency in Hz | 50-60 |
| Accessories included | |
| Mains cable | No |
| Wok ring | • |
| Small trivet | • |

KM 3034-1

Gas hob

with electronic functions for maximum safety and user convenience.



KM 3034-1 G (Installation drawing)

1. Front, 2. Casing depth, 3. Mains connection box with mains connection cable L = 2000 mm, 4. Gas connection R 1/2" - ISO 7-1 (DIN EN 10226)