

KM 2357-1

Gas hob

with electronic functions for maximum safety and user convenience.



- Optimal – single-handed operation via rotary dials and QuickStart
- Professional design – 892 mm wide stainless steel trough
- Particularly versatile – 5 burners incl. 1 dual wok
- Extremely safe – GasStop&Restart function
- Easy cleaning – dishwasher-safe ComfortClean pot rests

EAN: 4002516120094 / Material number: 10940180 / Old Material Number: 26235761GB

Heating type	
Heating type	Gas
Construction type	
Independent of cooker	•
Design	
Cast iron pot rests (matt black enamelled)	•
Miele logo embossed in stainless steel	•
Flush-fit stainless steel hob	•
Cooking zone details	
Number of cooking zones	5
Gas burner power rating	
Small burner in kW	1.00
Medium burner in kW	1.70
Large burner in kW	2.70
Dual wok burner in kW	4.50
1st cooking zone/cooking area	
Position	front left
Type	Economy burner
2nd cooking zone/cooking area	
Position	rear left
Type	High-speed burner
3rd cooking zone/cooking area	
Position	Centred
Type	Dual wok burner
4th cooking zone/cooking area	
Position	rear right
Type	Standard burner
5th cooking zone/cooking area	
Position	front right
Type	Standard burner
User convenience	
Operation via knobs	•
Electronic ignition with single-hand operation	•
QuickStart	•
Cleaning and care	
Dishwasher-proof pot rests	•
Safety	
GasStop & ReStart	•
Technical data	
Dimensions (H x W x D) in mm	105 x 892 x 512
Dimensions in mm (width)	892
Dimensions in mm (height)	105
Dimensions in mm (depth)	512
Cut-out dimensions (W x D) with flush-fit installation in mm	880/892 x 500/512
Cutout dimensions in mm (width) with surface-mounted installation	880
Cutout dimensions in mm (depth) with surface-mounted installation	500
Casing height incl. connection box in mm	101
Internal cutout dimensions in mm (width) with flush installation	880

KM 2357-1

Gas hob

with electronic functions for maximum safety and user convenience.



EAN: 4002516120094 / Material number: 10940180 / Old Material Number: 26235761GB

Internal cutout dimensions in mm (depth) with flush installation	500
Weight in kg	20
External cutout dimensions in mm (width) with flush installation	892
External cutout dimensions in mm (depth) with flush installation	512
Total rated load in kW	0.00-0.00
Length of supply lead in m	1.4
Dimensions in mm (width)	Hinten links
Voltage in V	220-240
Frequency in Hz	50-60
<b>Accessories included</b>	
Mains cable	No
Jets for liquid gas	•
Wok ring	•
Small trivet	•