

H 2267-1 BP Active

Oven

with a timer, pyrolytic cleaning & FlexiClip runners.



- 7-segment display with retractable rotary controls – EasyControl
- Minimal cleaning effort – Pyrolytic cleaning
- Lots of room and flexibility – 76 l oven capacity on 5 levels
- Easy handling – FlexiClip runners
- Protects against burns – touch-cool fronts



EAN: 4002516156710 / Material number: 11093000 /
Old Material Number: 22226795GB

General information	
Model identifier	H 2267-1 BP Active
Manufacturer material number	11093000
EAN number	4002516156710
Marketing class	Silver
Construction type and design	
Built-in oven	•
Colour	Stainless steel/Clean Steel
Retractable rotary controls	•
Convenience features	
Rapid heat-up	•
Operating modes	
Fan plus	•
Conventional heat	•
Intensive bake	•
Fan grill	•
Grill	•
Bottom heat	•
User convenience	
Display	EasyControl
Time of day display	•
Minute minder	•
Programmable end of cooking duration	•
Programmable cooking duration	•
Actual temperature display	•
Target temperature display	•
Buzzer when desired temperature is reached	•
Recommended temperature	•
Individual settings	•
Efficiency	
Energy efficiency class (A+++ – D)	A+
Cleaning and care	
Stainless steel/CleanSteel finish	•
Pyrolytic self-cleaning	•
Hinged grill element	•
CleanGlass door	•
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Door lock during pyrolytic cleaning	•
Technical data	
Oven compartment volume in l	76
No. of shelf levels	5
Numbered shelf levels	•
Mains plug	3 pole without plug
Oven light	1 halogen spot
Niche width min. in mm	560

H 2267-1 BP Active

Oven

with a timer, pyrolytic cleaning & FlexiClip runners.



EAN: 4002516156710 / Material number: 11093000 /
Old Material Number: 22226795GB

Niche width max. in mm	568
Niche height min. in mm	590
Niche height max. in mm	595
Niche depth in mm	550
Weight in kg	47.0
Total rated load in kW	3.60
Voltage in V	220 - 240
Frequency in Hz	50
Fuse rating in A	16
Number of phases	1
Length of mains connection cable in m	1.50
Replacing lamps	Customer


Accessories included

Baking tray with PerfectClean	1
Universal tray with PerfectClean HUBB 71	1
Baking and roasting rack without PerfectClean	1
FlexiClip runners HFC 70-C (pair)	1
Removable side runners (pair)	1
Grilling and roasting insert with PerfectClean	1

H 2267-1 BP Active


Oven

with a timer, pyrolytic cleaning & FlexiClip runners.




installation H7000 XL, installation drawing

1) Netzanschlussleitung, L=1500 mm, 2) In diesem Bereich kein Anschluss, 3) Lüftungsausschnitt min. 150 cm²




installation H7000 XL, installation drawing, GB, AU

1) Netzanschlussleitung, L=1500 mm, 2) In diesem Bereich kein Anschluss, 3) Lüftungsausschnitt min. 150 cm²




side view H7000 XL, installation drawings, GB, AU

22 mm – glass, 23.3 mm – metal




built-in H7000 XL, installation drawing




Installation H7000 XL underframe, installation drawings

If the oven is to be installed under a hob, follow the instructions for installing the hob and the height of the hob.




H226x-1B/BP/E/EP/I/IP, H24xx installation drawings

1) 400 mm, 2) 360 mm, 3) 42 mm, 4) 27 mm, 5) 32.5 mm




Installation H7000 BM XL, installation drawings



side view H7000 XL build-under, installation drawing, GB, AU

22 mm – glass, 23.3 mm – metal




Side view Kombi BM XL, installation drawings

22 mm – glass, 23.3 mm – metal

H 2267-1 BP Active

Oven

with a timer, pyrolytic cleaning & FlexiClip runners.



Installation Kombi BM XL, installation drawings

22 mm – glass, 23,3 mm – metal