

M 7240 TC

Built-in microwave oven

in a design that is the perfect complement with controls on the top.



- Clear-text display with sensor controls – DirectSensor S
- Perfect defrosting and cooking – Automatic programmes
- Plenty of room – 46 l oven compartment volume and 40 cm turntable
- Very powerful microwave – 900 W
- Popcorn at the touch of a button – Popcorn button

EAN: 4002516103356 / Material number: 11093950 /

Old Material Number: 24724040GB









Construction type and design	
Appliance colour	Stainless steel/Clean Steel
PureLine	•
TopControl	•
Construction type and design	
Built-in microwave oven	•
Convenience features	
Keeping warm	•
Operating modes	
Microwave	•
Automatic programmes	•
User convenience	
Display	DirectSensor S
SoftOpen	•
SoftClose	•
MultiLingua	•
Popcorn function	•
Time of day display	•
Minute minder	•
Programmable end of cooking duration	•
Programmable cooking duration	•
Quick microwave	•
Individual settings	•
Efficiency and sustainability	
Power rating in off mode in W	0.3
Power rating in standby mode in W	0.8
Night dimming	•
Time until automatic switch to standby in min	20
Time until automatic switch to off mode in min	20
Cleaning and care	
Stainless steel/CleanSteel finish	•
Stainless steel oven compartment	•
CleanGlass door	•
Safety	
System lock	•
Safety switch-off	•
Safety lock "Door" warning	•
Technical data	
Oven compartment volume in l	46
Appliance dimensions (W x H x D) in mm	595 x 456 x 560
Door hinge	Bottom
Oven light	1 LED spot
Turntable diameter in cm	40.6
Oven interior height in cm	23.2
Electronically controlled microwave power	•
Microwave power levels in W	
Maximum microwave power in W	900
Niche width min. in mm	562

Built-in microwave oven

in a design that is the perfect complement with controls on the top.




Old Material Number: 24724040GB

Niche width max. in mm	568
Niche height min. in mm	450
Niche height max. in mm	452
Niche depth in mm	550
Niche-independent venting	•
Appliance width in mm	595
Appliance height in mm	456
Appliance depth in mm	560
Weight in kg	28.3
Total rated load in kW	1.6
Voltage in V	220-240
Length of supply lead in m	2.10
Frequency in Hz	50
Fuse rating in A	13
Number of phases	1
Neutral conductor	Yes
Mains cable with plug	•
Replacing lamps	Service
Accessories included	
Turntable	1
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, portuguese, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,  ,  ,  ,  ,  ,  ,  , 


M 7240 TC

Built-in microwave oven


in a design that is the perfect complement with controls on the top.



M7140TC, M724x, installation drawings




M7140TC, M724xTC, installation drawing




M7140TC, M724xTC, installation drawing

22 mm – glass, 23.3 mm – stainless steel




M7140TC, M724x, installation drawings

1) Front view, 2) Mains connection cable L=1,600 mm, 3)
No connection in this area



M7140TC, M724x, installation drawings

1) Front view, 2) Mains connection cable L=1,600 mm, 3)
No connection in this area



M7140TC, M724x, installation drawings