

PTD 703 [DOS]

Tank dishwasher

with short cycles for fast turnaround times - incl. integr. cleaning agent containers.



- Max. cleaning performance: 1170 plates/h
- Simple and flexible operation – full-touch display
- Economical and efficient – water consumption of only 2.00 l* per cycle
- Always the right programme – item-specific solutions
- Perfect integration – suitable for installation in run of units

* The specified value refers to the ECO programme. Water consumption depends on the selected programme.

EAN: 4002516104346 / Material number: 11097740 / Old Material Number: 61070303D

Construction type and version	
Construction type	Freestanding dishwasher, can be built under
Range	Professional
Wash system	Tank front loader
Number of levels	1
Front	Stainless steel
Lid	Stainless Steel
Side panels	Stainless steel
Rear panel	Plastic
Tank volume in l	15.3
Application	
Suitable for retirement and care homes	•
Suitable for small restaurants/bars	•
Suitable for hospitality industry	•
Suitable for guesthouses	•
Suitable for canteens	•
Suitable for child care facilities	•
Suitable for universities and schools	•
Suitable for small businesses	•
Suitable for fast food restaurants	•
Suitable for sports clubs	•
Performance data	
Tested virucidal efficacy	•
Circulation pump Qmax in l/min.	200
Shortest programme duration in sec.	55
Maximum final rinse temperature in °C	90
Cleaning performance, plates/h	1170
Cleaning performance, baskets/h	66
Service life in wash cycles	250000
Control system	
Control system	Electronic controls
Programme selection	Full-touch display
Automatic On/Off standby switch	•
Programmes [number]	4
Coloured programme sequence indicator	•
Choice of display language	•
Standard electrical connection	
Electrical connection	3N AC 380-415V 50HZ
Heater rating in kW	0.00
Tank heater rating in kW	1.80
Boiler heater rating in kW	4.90
Total connected load in kW	7.90
Fuse rating in A	16
Possible voltage variant 1	
Electrical connection	3 AC 230V 50HZ
Heater rating in kW	0.00
Total connected load in kW	5.00
Fuse rating in A	20

PTD 703 [DOS]

Tank dishwasher

with short cycles for fast turnaround times - incl. integr. cleaning agent containers.



EAN: 4002516104346 / Material number: 11097740 / Old Material Number: 61070303D

Possible voltage variant 2	
Electrical connection	3N AC 380-415V 50HZ
Heater rating in kW	0.00
Total connected load in kW	6.00
Fuse rating in A	10
Possible voltage variant 3	
Electrical connection	3 AC 230V 50HZ
Heater rating in kW	0.00
Total connected load in kW	7.30
Fuse rating in A	25
Possible voltage variant 4	
Electrical connection	AC 220-240V 50HZ
Heater rating in kW	0.00
Total connected load in kW	2.60
Fuse rating in A	13
Possible voltage variant 5	
Electrical connection	AC 220-240V 50HZ
Heater rating in kW	0.00
Total connected load in kW	3.20
Fuse rating in A	16
Possible voltage variant 6	
Electrical connection	AC 220-240V 50HZ
Heater rating in kW	0.00
Total connected load in kW	4.20
Fuse rating in A	20
Water connection/drainage	
Cold or hot water [number]	1
Required flow pressure in bar	1.00-6.00
Drain pump head height from floor level, max. in c	60
Maximum water hardness in mmol/l	0.53
Water consumption per wash cycle in l	2.00
Dimensions and weight	
External dimensions, height in mm	820
External dimensions, net width in mm	600
External dimensions, net depth in mm	637
External dimensions, gross height in mm	870
External dimensions, gross width in mm	650
External dimensions, gross depth in mm	667
Usable space in wash cabinet, height in mm	404
Usable space in wash cabinet, width in mm	510
Usable space in wash cabinet, depth in mm	568
In-feed height above floor in mm	328
Net weight [kg]	69
Gross weight in kg	79
Maximum floor load in N/m ²	790
Emissions data	
Emissions – sound pressure at workplace	55 dB(A) re 20 µPa
Programmes	
Programme for light soiling	•
Programme for normal soiling	•
Programme for heavy soiling	•

PTD 703 [DOS]

Tank dishwasher

with short cycles for fast turnaround times - incl. integr. cleaning agent containers.



EAN: 4002516104346 / Material number: 11097740 / Old Material Number: 61070303D

Additional programme options	•
Wash ware specific	•
Self-cleaning	•
Descaling	•
Basket design	
Without baskets	•
Features	
Integrated dispensing pump/dispensing module for rinsing agent	•
Integrated dispensing pump/dispensing module for liquid cleaning agent	•
Internal cleaning agent containers	•
Wash cabinet made from high-quality stai	•
Stainless steel rear panel of splash protection class IPX5 (optional)	•
Spray arm monitor for all spray arms	•
Adjustable final rinse temperature	•
Adjustable wash temperature	•
Adjustable rinse time	•
Temperature indicator for tank and boiler	•
Hygienic tank wash cabinet	•
Innovatove spray arms	•
A wide range of accessories (optional)	•
Standards, test certificates and symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
Splash-proof IPX3	•
DIN EN 17735	•