

## PDR 908 HP [EL]

Professional heat-pump dryer, Little Giants

With very low energy consumption and short running times. Load capacity 8.0 kg.



- Drum volume 130.00 l | 130.00 l, load capacity 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry
- Future-proof networking via WiFi

EAN: 4002516126621 / Material number: 11104460 / Old Material Number: 52908153GB

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance Plus
Front	Lotus white
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in l	130.00
Drying system	Heat pump
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	2.80
Specific energy consumption in kWh/kg	0.20
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.20
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.17
Programme duration in min.	79
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	79
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	67
Control system	
Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•

## PDR 908 HP [EL]

Professional heat-pump dryer, Little Giants

With very low energy consumption and short running times. Load capacity 8.0 kg.



EAN: 4002516126621 / Material number: 11104460 / Old Material Number: 52908153GB

Language can be selected easily at any time

### Standard electrical connection

Heating type	Heat pump
Electrical connection	220-240V~ 50HZ
Electric heater rating in kW	0.00-0.00
Total connected load in kW	1.44
Fuse rating in A	13

### Dimensions and weight of dryer

External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	777
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	71.0
Gross weight in kg	77
Maximum floor load in N/m <sup>2</sup>	920

### Emissions data

Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.60

### Features

Intelligent drum reversal	•
Axial airflow	•
Fluff filter in the door	•
Low-maintenance heat exchanger filter system	•
PerfectDry	•
SoftLift drum ribs	•
Gentle tumble function	•
Condensed water drainage	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•

### Efficiency and sustainability

Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R134a
Refrigerant quantity in kg	0.61
Refrigerant global warming potential in kg CO <sub>2</sub> e	1430
Appliance global warming potential in kg CO <sub>2</sub> e	872.00

### Connection options

Payment system (optional)	•
Optical interface for service access	•
LAN/WiFi module (optional)	•

### Standards, test certificates and symbols

CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•

PDR 908 HP [EL]

Professional heat-pump dryer, Little Giants

With very low energy consumption and short running times. Load capacity 8.0 kg.



EAN: 4002516126621 / Material number: 11104460 / Old Material Number: 52908153GB

Complies with Machinery Directive 2006/42/EC

•