

## KM 7262 FR

Induction hob with onset controls

with cooking/extended zone at an attractive entry-level price



- Easy operation – EasySelect
- 4 round cooking zones and one cooking/extended zone
- A width of 614 mm with stainless steel frame for surface installation
- Shortest heating-up times – TwinBooster

EAN: 4002516149231 / Material number: 11144010 / Old Material Number: 26726210GB

| Heating type                       |                   |
|------------------------------------|-------------------|
| Heating type                       | Induction         |
| Construction type                  |                   |
| Independent of cooker              | •                 |
| Design                             |                   |
| Elegant glass ceramic surface      | •                 |
| Ceramic surface colour             | Black             |
| Stainless steel frame              | •                 |
| Surface-mounted installation       | •                 |
| Cooking zone details               |                   |
| Number of cooking zones            | 4                 |
| Number of cooking areas            | 0                 |
| Maximum number of pans             | 4                 |
| 1st cooking zone/cooking area      |                   |
| Position                           | front left        |
| Type                               | Dual-circuit ring |
| Size in mm                         | Ø 160-220         |
| Max. Booster power rating in W     | 3000              |
| Max. rating in W                   | 2300              |
| Max. TwinBooster power rating in W | 3650              |
| 2nd cooking zone/cooking area      |                   |
| Position                           | rear left         |
| Type                               | Dual-circuit ring |
| Size in mm                         | Ø 100-160         |
| Max. Booster power rating in W     | 1700              |
| Max. rating in W                   | 1400              |
| Max. TwinBooster power rating in W | 2200              |
| 3rd cooking zone/cooking area      |                   |
| Position                           | rear right        |
| Type                               | Casserole area    |
| Size in mm                         | Ø 190 / 190x290   |
| Max. Booster power rating in W     | 3000              |
| Max. rating in W                   | 2100              |
| Max. TwinBooster power rating in W | 3650              |
| 4th cooking zone/cooking area      |                   |
| Position                           | front right       |
| Type                               | Dual-circuit ring |
| Size in mm                         | Ø 140-190         |
| Max. Booster power rating in W     | 2500              |
| Max. rating in W                   | 1850              |
| Max. TwinBooster power rating in W | 3000              |
| User convenience                   |                   |
| Operation via sensor controls      | EasySelect        |
| Pan and pan size recognition       | •                 |
| Display colour                     | Yellow            |
| Auto heat-up                       | •                 |
| Permanent pan recognition          | •                 |
| Keeping warm                       | •                 |
| Stop & Go function                 | •                 |
| Recall function                    | •                 |

## KM 7262 FR

Induction hob with onset controls

with cooking/extended zone at an attractive entry-level price




EAN: 4002516149231 / Material number: 11144010 / Old Material Number: 26726210GB

|                                                                   |       |
|-------------------------------------------------------------------|-------|
| Safety switch-off                                                 | •     |
| Individual setting options (e.g. buzzers)                         | •     |
| Minute minder                                                     | •     |
| <b>Cleaning and care</b>                                          |       |
| Easy to clean ceramic glass                                       | •     |
| <b>Safety</b>                                                     |       |
| Safety switch-off                                                 | •     |
| Lock function                                                     | •     |
| System lock                                                       | •     |
| Integrated cooling fan                                            | •     |
| Overheating protection                                            | •     |
| Residual heat indicator                                           | •     |
| <b>Technical data</b>                                             |       |
| Dimensions in mm (width)                                          | 614   |
| Dimensions in mm (height)                                         | 51    |
| Dimensions in mm (depth)                                          | 514   |
| Cutout dimensions in mm (width) with surface-mounted installation | 600   |
| Cutout dimensions in mm (depth) with surface-mounted installation | 500   |
| Casing height incl. connection box in mm                          | 48    |
| Weight in kg                                                      | 10    |
| Total rated load in kW                                            | 7.30  |
| Length of supply lead in m                                        | 1.4   |
| Voltage in V                                                      | 230   |
| Frequency in Hz                                                   | 50-60 |
| <b>Accessories included</b>                                       |       |
| Mains cable                                                       | Yes   |

## KM 7262 FR

### Induction hob with onset controls

with cooking/extended zone at an attractive entry-level price



KM 7262 FR (installation drawing)

1) Front, 2) Mains connection box. Mains connection cable  
L = 1440 mm, supplied loose

L = 1440 mm, supplied loose