

## PWM 506 Mop Star 60 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve designed to meet the needs of facility management. Load capacity 6.0 kg.



- Drum volume 57 l, load capacity 6.0 kg
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Thorough cleaning – special programmes for mops and cloths
- Best possible dirt removal – patented pre-spin\*

\* Patent: EP 2 003 236 B1

EAN: 4002516134091 / Material number: 11154220 / Old Material Number: 51506264IRL

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance
Front	Lotus white
Control panel colour	Stainless steel
Load in kg	6.0
Drum volume in l	57
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated drum rear panel	•
Application	
Suitable for facility management	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	8.70
Specific energy consumption for cold water connection in kWh/kg	0.17
Specific water consumption for hot water connection in l/kg	8.20
Specific energy consumption for hot water connection in kWh/kg	0.06
Water consumption with cold water connection in l	52.0
Water consumption for cold water connection in Mops standard 60 °C programme in l	70.0
Energy consumption with cold water connection in kW	1.00
Energy consumption for cold water connection in Mops standard 60 °C programme in kWh	1.40
Programme duration in minutes with cold water connection	59
Water consumption with hot water connection in l	49.0
Energy consumption with hot water connection in kW	0.36
Programme duration in minutes with cold water and hot water connection	49
Residual moisture with cold rinse in %	52
Residual moisture with hot rinse in %	50
Residual moisture when processing cleaning cloths in %	20
Spin speed in rpm	1400
g factor	535
Control system	
Control system	M Select
Programmability	programmable
Max. delay start in h	96
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•
Dispensing	
Detergent drawer	3 compartments
Flexible dispensing adapter (optional)	•

## PWM 506 Mop Star 60 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve designed to meet the needs of facility management. Load capacity 6.0 kg.



EAN: 4002516134091 / Material number: 11154220 / Old Material Number: 51506264IRL

Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	~230V 50HZ
Heater rating in kW	4.60
Total connected load in kW	4.80
Fuse rating in A	25
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Dump valve	DN 70
<b>Dimensions and weight</b>	
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	714
External dimensions, gross height in mm	944
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	768
Net weight in kg	99.0
Gross weight in kg	104
Maximum floor load in N/m <sup>2</sup>	2820
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.00
<b>Features</b>	
Patented pre-spin	•
Cloth reprocessing	•
3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
Efficient drum rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
Communication slot	•
Add laundry	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	95
<b>Connection options</b>	
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFiConn@ct	•

## PWM 506 Mop Star 60 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve designed to meet the needs of facility management. Load capacity 6.0 kg.



EAN: 4002516134091 / Material number: 11154220 / Old Material Number: 51506264IRL

### Capacities

Cotton mops, 40 cm / 190 g [number]	31
Cotton mops, 50 cm / 220 g [number]	27
Microfibre mops, 40 cm / 120 g [number]	50
Microfibre mops, 50 cm / 170 g [number]	35

### Standards, test certificates and symbols

CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
UKCA	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•