

PWM 907 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve and target group specific programmes. Capacity 7.0 kg in 49 min.



- Drum volume 64 l, load capacity 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience w. full-touch colour display –M Touch Flex
- 22 % less water consumption and 28 % less energy consumption*
- Future-proof networking via WiFi

* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

EAN: 4002516197102 / Material number: 11154410 / Old Material Number: 51907251IRL

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance Plus
Front	Lotus white
Control panel colour	Stainless steel
Load in kg	7.0
Drum volume in l	64
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated drum rear panel	•
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for launderettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	7.00
Specific energy consumption for cold water connection in kWh/kg	0.14
Specific water consumption for hot water connection in l/kg	6.60
Specific energy consumption for hot water connection in kWh/kg	0.06
Water consumption with cold water connection in l	49.0
Energy consumption with cold water connection in kW	0.98
Programme duration in minutes with cold water connection	59
Water consumption with hot water connection in l	46.0
Energy consumption with hot water connection in kW	0.44
Programme duration in minutes with cold water and hot water connection	49
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704

PWM 907 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve and target group specific programmes. Capacity 7.0 kg in 49 min.



EAN: 4002516197102 / Material number: 11154410 / Old Material Number: 51907251IRL

Tested operating hours	30000
Control system	
Control system	M Touch Flex
Programmability	programmable
Max. delay start in h	96
Time left display	•
Programme sequence indicator	•
Language can be selected easily at any time	•
Dispensing	
Detergent drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (optional)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
Standard electrical connection	
Heating type	Electric
Electrical connection	2N~ 400V 50HZ
Heater rating in kW	5.30
Total connected load in kW	5.50
Fuse rating in A	13
Possible voltage variant 1	
Electrical connection	230V~
Heater rating in kW	2.65
Total connected load in kW	2.85
Fuse rating in A	13
Water connection/drainage	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Dump valve	DN 70
Dimensions and weight	
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	714
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	768
Net weight in kg	102.0
Gross weight in kg	106
Maximum floor load in N/m ²	2820
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.00
Features	
3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•

PWM 907 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve and target group specific programmes. Capacity 7.0 kg in 49 min.



EAN: 4002516197102 / Material number: 11154410 / Old Material Number: 51907251IRL

Pre-ironing	•
Efficient drum rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Machine-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	95
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•
Standards, test certificates and symbols	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•