

PDR 908 [EL MAR 3 AC 400-480V 50-60Hz]  
 Vented dryer, electrically heated  
 Lloyd's Register approved, load size 8.0 kg kg.



- Drum volume 130.00 l | 130.00 l, load capacity 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516227311 / Material number: 11250970 / Old Material Number: 52908487MAR

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Fascia color	Stainless steel
Drum volume in l	130.00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Maximum evaporation capacity in l/hour	4.80
Specific energy consumption in kWh/kg	0.50
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.50
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.42
Programme duration in min.	52
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	52
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	47
Control system	
Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Language can be selected easily at any time	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3~ 440V 50/60HZ
Electric heater rating in kW	5.16
Total connected load in kW	5.40
Fuse rating in A	10
Possible voltage variant 1	
Electrical connection	3~ 400V 50/60HZ
Heater rating in kW	4.26
Total connected load in kW	4.50
Fuse rating in A	10
Possible voltage variant 2	
Electrical connection	3~ 480V 50/60HZ
Heater rating in kW	6.14
Total connected load in kW	6.40
Fuse rating in A	10

PDR 908 [EL MAR 3 AC 400-480V 50-60Hz]  
 Vented dryer, electrically heated  
 Lloyd's Register approved, load size 8.0 kg kg.



EAN: 4002516227311 / Material number: 11250970 / Old Material Number: 52908487MAR

<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	69.0
Gross weight in kg	75
Maximum floor load in N/m <sup>2</sup>	920
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0.76
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•
<b>Standards, test certificates and symbols</b>	
CE	•
Splash-proof safety rating IPX4	•
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•