

PDR 908 [EL MAR 3N AC 400V 50-60Hz]  
 Vented dryer, electrically heated  
 Lloyd's Register approved, load size 8.0 kg kg.



- Drum volume 130.00 l | 130.00 l, load capacity 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516218463 / Material number: 11251050 / Old Material Number: 52908482MAR

| Construction type and version  |                              |
|--|------------------------------|
| Construction type  | Front loader                 |
| Range  | Performance Plus             |
| Front  | Stainless steel              |
| Fascia color   | Stainless steel              |
| Drum volume in l   | 130.00                       |
| Drying system  | Exhaust air                  |
| Door opening [Ø] in mm   | 370                          |
| Door opening angle in degrees  | 167                          |
| Door hinge   | left                         |
| Stainless steel honeycomb drum   | Yes                          |
| Application  |                              |
| Suitable for offshore use  | •                            |
| Suitable for marine use  | •                            |
| Performance data   |                              |
| Maximum evaporation capacity in l/hour   | 5.50                         |
| Specific energy consumption in kWh/kg  | 0.50                         |
| Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW | 0.50                         |
| Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a | 0.42                         |
| Programme duration in min.   | 42                           |
| Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes     | 42                           |
| Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in | 37                           |
| Control system   |                              |
| Control system   | M Touch Flex                 |
| Programmability  | programmable                 |
| User interface   | Residual moisture controlled |
| Max. delay start in h  | 24                           |
| Time left display  | •                            |
| Programme sequence indicator   | •                            |
| Language can be selected easily at any time  | •                            |
| Standard electrical connection   |                              |
| Heating type   | Electric                     |
| Electrical connection  | 3N~ 400V 50/60HZ             |
| Electric heater rating in kW   | 6.14                         |
| Total connected load in kW   | 6.40                         |
| Fuse rating in A   | 10                           |
| Possible voltage variant 1   |                              |
| Electrical connection  | 230V~ 50/60HZ                |
| Heater rating in kW  | 2.90                         |
| Total connected load in kW   | 3.24                         |
| Fuse rating in A   | 16                           |
| Possible voltage variant 2   |                              |
| Electrical connection  | 3~ 230V 50/60HZ              |
| Heater rating in kW  | 6.14                         |
| Total connected load in kW   | 6.40                         |
| Fuse rating in A   | 16                           |

PDR 908 [EL MAR 3N AC 400V 50-60Hz]

Vented dryer, electrically heated

Lloyd's Register approved, load size 8.0 kg kg.



EAN: 4002516218463 / Material number: 11251050 / Old Material Number: 52908482MAR

| <b>Dimensions and weight of dryer</b>           |                     |
|---|---------------------|
| External dimensions, height in mm               | 850                 |
| External dimensions, width in mm                | 605                 |
| External dimensions, depth in mm                | 717                 |
| External dimensions, gross height in mm         | 940                 |
| External dimensions, gross width in mm          | 660                 |
| External dimensions, gross depth in mm          | 820                 |
| Net weight in kg                                | 51.5                |
| Gross weight in kg                              | 57                  |
| Maximum floor load in N/m <sup>2</sup>          | 920                 |
| <b>Emissions data</b>                           |                     |
| Emission sound pressure level in the workplace  | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h          | 0.76                |
| <b>Features</b>                                 |                     |
| Intelligent drum reversal                       | •                   |
| Axial airflow                                   | •                   |
| Large-surface filter                            | •                   |
| PerfectDry                                      | •                   |
| SoftLift drum ribs                              | •                   |
| Low temperature function                        | •                   |
| Communication slot                              | •                   |
| Drying basket (optional)                        | •                   |
| Drum lighting                                   | •                   |
| Machine-independent accessories                 | •                   |
| <b>Connection options</b>                       |                     |
| Payment system (optional)                       | •                   |
| Optical interface for service access            | •                   |
| Peak load cut-out/energy management (optional)  | •                   |
| LAN/WiFi module (optional)                      | •                   |
| WiFiConn@ct                                     | •                   |
| <b>Standards, test certificates and symbols</b> |                     |
| CE  | •                   |
| Splash-proof safety rating IPX4                 | •                   |
| WEEE  | •                   |
| Lloyd's Register                                | •                   |
| Complies with Machinery Directive 2006/42/EC    | •                   |