

PDR 507 HP [MAR]

Heat-pump dryers

Lloyd's Register approved, load size 7.0 kg kg.



- Drum volume 130.00 l | 130.00 l, load capacity 7.0 kg
- 50 % less energy consumption than vented dryers*
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

* Heat pump dryers consume up to 50 % less energy than an electrically heated vented dryer.

EAN: 4002516246930 / Material number: 11300970 / Old Material Number: 52507188MAR

Construction type and version

Construction type	Front loader
Range	Performance
Front	Lotus white
Fascia color	Stainless steel
Load in kg	7.0
Drum volume in l	130.00
Drying system	Heat pump
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes

Application

Suitable for offshore use	•
Suitable for marine use	•

Performance data

Maximum evaporation capacity in l/hour	2.70
Specific energy consumption in kWh/kg	0.20
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.20
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.17
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	67
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	57

Control system

Control system	M Select
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•

Standard electrical connection

Heating type	Heat pump
Electrical connection	230V~ 60HZ
Electric heater rating in kW	0.00
Total connected load in kW	1.20
Fuse rating in A	10
Provided with plug	•

Dimensions and weight of dryer

External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	777
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	68.5

PDR 507 HP [MAR]

Heat-pump dryers

Lloyd's Register approved, load size 7.0 kg kg.



EAN: 4002516246930 / Material number: 11300970 / Old Material Number: 52507188MAR

Gross weight in kg	74
Maximum floor load in N/m ²	920
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.60
Features	
Intelligent drum reversal	•
Axial airflow	•
Fluff filter in the door	•
Low-maintenance heat exchanger filter system	•
PerfectDry	•
SoftLift drum ribs	•
Gentle tumble function	•
Condensed water drainage	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
Efficiency and sustainability	
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R134a
Refrigerant quantity in kg	0.59
Refrigerant global warming potential in kg CO ₂ e	1430
Appliance global warming potential in kg CO ₂ e	844.00
Connection options	
Payment system (optional)	•
Optical interface for service access	•
LAN/WiFi module (optional)	•
Standards, test certificates and symbols	
CE	•
VDE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•