

PT 7186 Vario XL [EL 1N AC 230-240V 50Hz]

Vented dryer, electrically heated

with a shortest cycle time of 41 min 41 min for a high throughput of laundry.



- Drum volume 180.00 l 180.00 l, load capacity 9.0 kg
- Large programme variety – application-specific drying programmes
- Precision drying of all fabrics – PerfectDry
- Unique, gentle fabric care – honeycomb drum
- Easy operation – viewing window and large-surface filter

EAN: 4002516236849 / Material number: 11331700 / Old Material Number: 527186X5GB

Construction type and design	
Construction type	Front loader
Range	Octoplus
Front	Octo blue
Load in kg	9.0
Load ratio	1:20
Drum volume in l	180.00
Drying system	Exhaust air
Door opening [Ø] in mm	440
Door opening angle in degrees	180
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Performance data	
Maximum evaporation capacity in l/hour	8.10
Programme duration in min.	41
Controls	
Control system	Profitronic L Vario
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard/target grp programmes	
Basic programmes	•
Programmes for facility management	•
Programmes for dry cleaners	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for domestic use	•
Standard electrical connection	
Heating type	Electric

PT 7186 Vario XL [EL 1N AC 230-240V 50Hz]

Vented dryer, electrically heated

with a shortest cycle time of 41 min 41 min for a high throughput of laundry.



EAN: 4002516236849 / Material number: 11331700 / Old Material Number: 527186X5GB

Electrical connection	AC 230-240V 50HZ
Electric heater rating in kW	5.22-5.68
Total connected load in kW	5.78-6.24
Fuse rating in A	25
Dimensions and weight	
External dimensions, height in mm	1020
External dimensions, width in mm	700
External dimensions, depth in mm	763
External dimensions, gross height in mm	1215
External dimensions, gross width in mm	760
External dimensions, gross depth in mm	820
Net weight in kg	77.0
Gross weight in kg	88
Maximum floor loading in N	1020
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.62
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Machine-independent accessories	•
Connection options	
Payment system	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
Capacities	
Respirator masks [number]	4
Overalls [number]	1
Over jackets [number]	1-2
Synthetic duvets [number]	1
Synthetic pillows [number]	1-2
Down duvets [number]	1
Down pillows [number]	1-2
Cloths, 22 g [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	1-2
Standards, certs, symbols	
CE	•
VDE	•
Splash-proof safety rating IPX4	•
WEEE	•

Miele

PT 7186 Vario XL [EL 1N AC 230-240V 50Hz]

Vented dryer, electrically heated

with a shortest cycle time of 41 min 41 min for a high throughput of laundry.



EAN: 4002516236849 / Material number: 11331700 / Old Material Number: 527186X5GB

Complies with Machinery Directive 2006/42/EC

•