

PWM 508 Mop Star 80 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve designed to meet the needs of facility management. Load capacity 8.0 kg.



- Drum volume 73 l, load capacity 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Thorough cleaning – special programmes for mops and cloths
- Best possible dirt removal – patented pre-spin*

* Patent: EP 2 003 236 B1

EAN: 4002516373551 / Material number: 11395240 / Old Material Number: 51508263GB

| Construction type and version | |
|--|-------------------------|
| Construction type | Front-loader, stackable |
| Range | Performance |
| Front | Lotus white |
| Control panel colour | Stainless steel |
| Load in kg | 8.0 |
| Drum volume in l | 73 |
| Door opening [Ø] in mm | 300 |
| Door opening angle in degrees | 167 |
| Door hinge | right |
| Maintenance-free synchronous motor | • |
| Honeycomb drum with perforated drum rear panel | • |
| Application | |
| Suitable for facility management | • |
| Performance data | |
| Tested virucidal efficacy | • |
| Proven hygiene | • |
| Specific water consumption for cold water connection in l/kg | 7.60 |
| Specific water consumption for cold water connection in Mops standard 60 °C programme in l/kg | 12.60 |
| Specific energy consumption for cold water connection in kWh/kg | 0.16 |
| Specific energy consumption for cold water connection in Mops standard 60 °C programme in kWh/kg | 0.21 |
| Specific water consumption for hot water connection in l/kg | 7.25 |
| Specific energy consumption for hot water connection in kWh/kg | 0.06 |
| Water consumption with cold water connection in l | 61.0 |
| Energy consumption with cold water connection in kW | 1.30 |
| Energy consumption for cold water connection in Mops standard 60 °C programme in kWh | 1.70 |
| Programme duration in minutes with cold water connection | 59 |
| Water consumption with hot water connection in l | 58.0 |
| Energy consumption with hot water connection in kW | 0.48 |
| Energy consumption for hot water connection in Mops standard 60 °C programme in kWh | 0.60 |
| Programme duration in minutes with cold water and hot water connection | 49 |
| Programme running time in minutes for Mops standard 60 °C programme with hot water connection | 47 |
| Residual moisture with cold rinse in % | 52 |
| Residual moisture with hot rinse in % | 50 |
| Residual moisture when processing cleaning cloths in % | 20 |
| Spin speed in rpm | 1400 |
| g factor | 535 |
| Control system | |
| Control system | M Select |
| Programmability | programmable |
| Max. delay start in h | 96 |
| Time left display | • |
| Programme sequence indicator | • |

PWM 508 Mop Star 80 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve designed to meet the needs of facility management. Load capacity 8.0 kg.



EAN: 4002516373551 / Material number: 11395240 / Old Material Number: 51508263GB

| | |
|---|--------------------------------|
| Control panel with easy-to-understand symbols | • |
| Language can be selected easily at any time | • |
| Dispensing | |
| Detergent drawer | 3 compartments |
| Flexible dispensing adapter (optional) | • |
| Maximum number of connections for liquid dispenser pumps [number] | 6 |
| Empty sensor | • |
| Standard electrical connection | |
| Heating type | Electric |
| Electrical connection | 230V~ |
| Heater rating in kW | 2.30 |
| Total connected load in kW | 2.50 |
| Fuse rating in A | 13 |
| Possible voltage variant 1 | |
| Electrical connection | 2N~ 400V 50HZ |
| Heater rating in kW | 4.60 |
| Total connected load in kW | 4.80 |
| Fuse rating in A | 13 |
| Water connection/drainage | |
| Cold water [number] | 1x 1/2" hose w/ 3/4" th. union |
| Hot water [number] | 1x 1/2" hose w/ 3/4" th. union |
| Dump valve | DN 70 |
| Dimensions and weight | |
| External dimensions, height in mm | 850 |
| External dimensions, width in mm | 596 |
| External dimensions, depth in mm | 714 |
| External dimensions, gross height in mm | 944 |
| External dimensions, gross width in mm | 660 |
| External dimensions, gross depth in mm | 768 |
| Net weight in kg | 101.0 |
| Gross weight in kg | 105 |
| Maximum floor loading in N | 2820 |
| Emissions data | |
| Emission sound pressure level in the workplace | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 1.00 |
| Features | |
| Patented pre-spin | • |
| Cloth reprocessing | • |
| 3-dimensional imbalance monitoring | • |
| Commercial shock absorbers | • |
| Hard-wearing stainless-steel flange | • |
| Disinfection rinse | • |
| EcoSpeed | • |
| Efficient drum rib technology | • |
| Temperature monitoring | • |
| Special heater element | • |
| Automatic load control | • |
| Flow meter | • |
| Communication slot | • |

PWM 508 Mop Star 80 [EL DV]

Professional washing machine, Little Giants, EL heated, with drain valve designed to meet the needs of facility management. Load capacity 8.0 kg.